



TRADEMASTER TOGGLE FAN SPEED CONTROL, WHITE

TSC5W | [Pass & Seymour](#)

FEATURES & BENEFITS

Toggle Fan Speed Control, 5amp White

- Tough, impact-resistant thermoplastic housing.
- Power-failure memory.
- Superior heat management: no time wasting break off tabs.
- Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.

SPECIFICATIONS

GENERAL INFO

Color: White

Product Series: TradeMaster

Type: Toggle

Special Features: Continuous Variable

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No

CUL Listing No: No

cULus: Yes

cURus: No

Federal Spec: No

UL Listing No: No

UN SPSC: 39121502

UR: No

DIMENSIONS

Weight: 0.19206

TECHNICAL INFORMATION

Volts: 120V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





TRADEMASTER TOGGLE FAN SPEED CONTROL, WHITE

TSC5W | [Pass & Seymour](#)

FEATURES & BENEFITS

Toggle Fan Speed Control, 5amp White

- Tough, impact-resistant thermoplastic housing.
- Power-failure memory.
- Superior heat management: no time wasting break off tabs.
- Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.

SPECIFICATIONS

GENERAL INFO

Color: White

Product Series: TradeMaster

Type: Toggle

Special Features: Continuous Variable

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No

CUL Listing No: No

cULus: Yes

cURus: No

Federal Spec: No

UL Listing No: No

UN SPSC: 39121502

UR: No

DIMENSIONS

Weight: 0.19206

TECHNICAL INFORMATION

Volts: 120V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

