



## TELESCOPING RIGID BOX SUPPORT, 16"–24" STUD SPACING

### CATALOG NUMBER

**TSRBS1625**



### CERTIFICATIONS



### FEATURES

Accommodates up to 6-gang box in 16" stud spacing or up to 10-gang in 24" stud spacing

Will support four electrical boxes in 24" stud spacing

Open design allows a variety of positions for box location

Easy to adjust after the electrical box is installed

For use with 4" square and 4-11/16" boxes and mud rings

Unique, one-piece, break apart design

### PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Stud Spacing: 16" - 24"

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**



## TELESCOPING RIGID BOX SUPPORT, 16"–24" STUD SPACING

### CATALOG NUMBER

**TSRBS1625**



### CERTIFICATIONS



### FEATURES

Accommodates up to 6-gang box in 16" stud spacing or up to 10-gang in 24" stud spacing

Will support four electrical boxes in 24" stud spacing

Open design allows a variety of positions for box location

Easy to adjust after the electrical box is installed

For use with 4" square and 4-11/16" boxes and mud rings

Unique, one-piece, break apart design

### PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Stud Spacing: 16" - 24"

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**