

## Specification Sheet

Part Number: TSRI-JB2



**Article Number**

250-10005

**Type**

TSR-JB2

**Color**

Ivory (IV)

**Features & Benefits**

- Tamper resistant, self-locking hidden positive latch permits quick re-entry as well as providing a secure installation of premise wire.
- Fittings incorporate a minimum 1" bend radius per ANSI/TIA-568-C and 569-A standards.
- Rubber-based, foam-tape adhesive with high ultimate bond strength conforms to any surface.
- Flexible hinge allows the raceway to endure numerous openings without creating discoloration or stress cracking

**Quantity Per**

bag

**Product Description**

Offered in dual or single gang format, HellermannTyton's Low Voltage Junction Boxes are versatile enough for any network cabling application. Available in varying depths, these boxes are all equipped with concentric knockouts on all four sides for every TSR size of raceway to eliminate routing and installation inconvenience. All junction boxes come with adhesive strips on the back of the base and #6 screws to secure the box to the base.

**Short Description**

Single Gang Junction Box, 2" Deep, PVC, Ivory, 1/bag

**Global Part Name**

TSR-JB2-PVC-BGE

**Length L (Imperial)**

4.75

**Length L (Metric)**

120.65

**Width W (Imperial)**

3.0

**Width W (Metric)**

76.2

**Height H (Imperial)**

2.0

**Height H (Metric)**

50.80

**Material**

Polyvinylchloride (PVC)

**Material Shortcut**

PVC

**Flammability**

UL 94 V0

**Halogen free**

No

**Operating Temperature (Metric)**

+122°F (+50°C)

**Reach Complaint(Article 33)**

No

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

1

**Package Quantity (Metric)**

1

**Customs Number**

3925900000