

844-200-MAKO
405-509-2665
mako-products.net



Domestic & Import
Seamless & Welded
304SS, 316SS, Alloys
Sticks & Coils



Import Sticks

STICKS - WELDED 304SS - 10' or 20' LENGTHS

PART NUMBER	OD	WALL	PRICE	LIST
TWS-304-250-35-20	1/4"	0.035		
TWS-304-375-35-20	3/8"	0.035		
TWS-304-375-49-20	3/8"	0.049		
TWS-304-500-35-20	1/2"	0.035		
TWS-304-500-49-20	1/2"	0.049		
TWS-304-750-49-20	3/4"	0.049		
TWS-304-750-83-20	3/4"	0.083		
TWS-304-875-49-20	7/8"	0.049		
TWS-304-1000-83-20	1"	0.083		

STICKS - SEAMLESS 304SS - 10' or 20' LENGTHS

PART NUMBER	OD	WALL	PRICE	LIST
TSS-304-250-35-20	1/4"	0.035		
TSS-304-250-49-20	1/4"	0.049		
TSS-304-375-35-20	3/8"	0.035		
TSS-304-375-49-20	3/8"	0.049		
TSS-304-375-65-20	3/8"	0.065		
TSS-304-500-35-20	1/2"	0.035		
TSS-304-500-49-20	1/2"	0.049		
TSS-304-500-65-20	1/2"	0.065		
TSS-304-625-35-20	5/8"	0.035		
TSS-304-625-65-20	5/8"	0.065		
TSS-304-625-83-20	5/8"	0.083		
TSS-304-750-65-20	3/4"	0.065		
TSS-304-750-83-20	3/4"	0.083		
TSS-304-750-120-20	3/4"	0.120		
TSS-304-1000-35-20	1"	0.035		
TSS-304-1000-65-20	1"	0.065		
TSS-304-1000-83-20	1"	0.083		
TSS-304-1000-109-20	1"	0.109		
TSS-304-1000-120-20	1"	0.120		
TSS-304-1250-65-20	1-1/4"	0.065		
TSS-304-1250-83-20	1-1/4"	0.083		
TSS-304-1250-120-20	1-1/4"	0.120		
TSS-304-1250-156-20	1-1/4"	0.156		
TSS-304-1500-65-20	1-1/2"	0.065		
TSS-304-1500-83-20	1-1/2"	0.083		
TSS-304-1500-120-20	1-1/2"	0.120		
TSS-304-1500-156-20	1-1/2"	0.156		
TSS-304-1500-250-20	1-1/2"	0.250		
TSS-304-2000-65-20	2"	0.065		
TSS-304-2000-83-20	2"	0.083		
TSS-304-2000-109-20	2"	0.109		
TSS-304-2000-120-20	2"	0.120		
TSS-304-2000-156-20	2"	0.156		

STICKS - SEAMLESS 316SS - 10' or 20' LENGTHS

PART NUMBER	OD	WALL	PRICE	LIST
TSS-316-125-28-20	1/8"	0.028		
TSS-316-125-35-20	1/8"	0.035		
TSS-316-250-28-20	1/4"	0.028		
TSS-316-250-35-20	1/4"	0.035		
TSS-316-250-49-20	1/4"	0.049		
TSS-316-250-65-20	1/4"	0.065		
TSS-316-375-35-20	3/8"	0.035		
TSS-316-375-49-20	3/8"	0.049		
TSS-316-375-65-20	3/8"	0.065		
TSS-316-375-83-20	3/8"	0.083		
TSS-316-500-35-20	1/2"	0.035		
TSS-316-500-49-20	1/2"	0.049		
TSS-316-500-65-20	1/2"	0.065		
TSS-316-625-35-20	5/8"	0.035		
TSS-316-625-49-20	5/8"	0.049		
TSS-316-625-65-20	5/8"	0.065		
TSS-316-625-83-20	5/8"	0.083		
TSS-316-750-35-20	3/4"	0.035		
TSS-316-750-49-20	3/4"	0.049		
TSS-316-750-65-20	3/4"	0.065		
TSS-316-750-83-20	3/4"	0.083		
TSS-316-750-95-20	3/4"	0.095		
TSS-316-750-109-20	3/4"	0.109		
TSS-316-750-120-20	3/4"	0.120		
TSS-316-1000-49-20	1"	0.049		
TSS-316-1000-65-20	1"	0.065		
TSS-316-1000-83-20	1"	0.083		
TSS-316-1000-120-20	1"	0.120		
TSS-316-1000-134-20	1"	0.134		
TSS-316-1000-156-20	1"	0.156		
TSS-316-1250-65-20	1-1/4"	0.065		
TSS-316-1250-83-20	1-1/4"	0.083		
TSS-316-1250-120-20	1-1/4"	0.120		
TSS-316-1250-156-20	1-1/4"	0.156		
TSS-316-1250-250-20	1-1/4"	0.250		
TSS-316-1500-65-20	1-1/2"	0.065		
TSS-316-1500-83-20	1-1/2"	0.083		
TSS-316-1500-120-20	1-1/2"	0.120		
TSS-316-1500-156-20	1-1/2"	0.156		
TSS-316-1500-250-20	1-1/2"	0.250		
TSS-316-2000-65-20	2"	0.065		
TSS-316-2000-83-20	2"	0.083		
TSS-316-2000-109-20	2"	0.109		
TSS-316-2000-120-20	2"	0.120		
TSS-316-2000-156-20	2"	0.156		

844-200-MAKO
405-509-2665
mako-products.net



Domestic & Import
Seamless & Welded
304SS, 316SS, Alloys
Sticks & Coils



Domestic Sticks

STICK - 316 SEAMLESS - 10'-20' LENGTHS - DOMESTIC

STICK - 304SS WELDED - 10'-20' LENGTHS - DOMESTIC

PART NUMBER	OD	WALL	PRICE	LIST
TWS-304-250-35-20D	1/4"	0.035		
TWS-304-375-35-20D	3/8"	0.035		
TWS-304-375-49-20D	3/8"	0.049		
TWS-304-500-35-20D	1/2"	0.035		
TWS-304-500-49-20D	1/2"	0.049		
TWS-304-625-49-20D	5/8"	0.049		
TWS-304-750-49-20D	3/4"	0.049		
TWS-304-750-65-20D	3/4"	0.065		
TWS-304-750-83-20D	3/4"	0.083		
TWS-304-1000-65-20D	1"	0.065		
TWS-304-1000-83-20D	1"	0.083		
TWS-304-1000-109-20D	1"	0.109		
TWS-304-1000-120-20D	1"	0.120		

STICK - 316SS WELDED - 10'-20' LENGTHS - DOMESTIC

PART NUMBER	OD	WALL	PRICE	LIST
TWS-316-250-35-20D	1/4"	0.035		
TWS-316-375-35-20D	3/8"	0.035		
TWS-316-500-35-20D	1/2"	0.035		
TWS-316-625-35-20D	5/8"	0.035		
TWS-316-750-49-20D	3/4"	0.049		
TWS-316-750-65-20D	3/4"	0.065		
TWS-316-1000-65-20D	1"	0.065		
TWS-316-1000-83-20D	1"	0.083		
TWS-316-1000-109-20D	1"	0.109		
TWS-316-1000-120-20D	1"	0.120		

STICK - 304SS SEAMLESS - 10'-20' LENGTHS - DOMESTIC

PART NUMBER	OD	WALL	PRICE	LIST
TSS-304-250-35-20D	1/4"	0.035		
TSS-304-250-49-20D	1/4"	0.049		
TSS-304-375-35-20D	3/8"	0.035		
TSS-304-375-49-20D	3/8"	0.049		
TSS-304-375-65-20D	3/8"	0.065		
TSS-304-500-35-20D	1/2"	0.035		
TSS-304-500-49-20D	1/2"	0.049		
TSS-304-500-65-20D	1/2"	0.065		

PART NUMBER	OD	WALL	PRICE	LIST
TSS-316-125-28-20D	1/8"	0.028		
TSS-316-250-35-20D	1/4"	0.035		
TSS-316-250-49-20D	1/4"	0.049		
TSS-316-250-28-20D	1/4"	0.028		
TSS-316-375-35-20D	3/8"	0.035		
TSS-316-375-49-20D	3/8"	0.049		
TSS-316-375-65-20D	3/8"	0.065		
TSS-316-375-83-20D	3/8"	0.083		
TSS-316-500-35-20D	1/2"	0.035		
TSS-316-500-49-20D	1/2"	0.049		
TSS-316-500-65-20D	1/2"	0.065		
TSS-316-625-35-20D	5/8"	0.035		
TSS-316-625-49-20D	5/8"	0.049		
TSS-316-625-65-20D	5/8"	0.065		
TSS-316-625-83-20D	5/8"	0.083		
TSS-316-750-35-20D	3/4"	0.035		
TSS-316-750-49-20D	3/4"	0.049		
TSS-316-750-65-20D	3/4"	0.065		
TSS-316-750-83-20D	3/4"	0.083		
TSS-316-750-109-20D	3/4"	0.109		
TSS-316-750-120-20D	3/4"	0.120		
TSS-316-1000-49-20D	1"	0.049		
TSS-316-1000-65-20D	1"	0.065		
TSS-316-1000-83-20D	1"	0.083		
TSS-316-1000-120-20D	1"	0.120		
TSS-316-1000-134-20D	1"	0.134		
TSS-316-1000-156-20D	1"	0.156		
TSS-316-1500-65-20D	1-1/2"	0.065		
TSS-316-1500-83-20D	1-1/2"	0.083		
TSS-316-1500-120-20D	1-1/2"	0.120		
TSS-316-1500-156-20D	1-1/2"	0.156		
TSS-316-1500-250-20D	1-1/2"	0.250		
TSS-316-1250-65-20D	1-1/4"	0.065		
TSS-316-1250-83-20D	1-1/4"	0.083		
TSS-316-1250-120-20D	1-1/4"	0.120		
TSS-316-1250-156-20D	1-1/4"	0.156		
TSS-316-1250-250-20D	1-1/4"	0.250		
TSS-316-2000-65-20D	2"	0.065		
TSS-316-2000-83-20D	2"	0.083		
TSS-316-2000-120-20D	2"	0.120		
TSS-316-2000-156-20D	2"	0.156		

Commodity Product - Prices subject to change

Additional sizes and types available- Call 405-509-2665

844-200-MAKO
405-509-2665
mako-products.net



Domestic & Import
Seamless & Welded
304SS, 316SS, Alloys
Sticks & Coils



Coils- Import & Domestic

COIL - 304SS - WELDED - .035 WALL - IMPORT

PART NUMBER	OD	LENGTH	PRICE	LIST
TWC-304-250-35-150	1/4"	150'		
TWC-304-250-35-300	1/4"	300'		
TWC-304-250-35-500	1/4"	500'		
TWC-304-375-35-150	3/8"	150'		
TWC-304-375-35-300	3/8"	300'		
TWC-304-375-35-500	3/8"	500'		
TWC-304-375-35-1000	3/8"	1000'		
TWC-304-500-35-150	1/2"	150'		
TWC-304-500-35-300	1/2"	300'		
TWC-304-500-35-500	1/2"	500'		
TWC-304-500-35-1000	1/2"	1000'		

COIL - 316SS - SEAMLESS - .035 WALL - IMPORT

PART NUMBER	OD	LENGTH	PRICE	LIST
TSC-316-250-35-150	1/4"	150'		
TSC-316-250-35-300	1/4"	300'		
TSC-316-250-35-500	1/4"	500'		
TSC-316-250-35-1000	1/4"	1000'		
TSC-316-375-35-150	3/8"	150'		
TSC-316-375-35-300	3/8"	300'		
TSC-316-375-35-500	3/8"	500'		
TSC-316-375-35-1000	3/8"	1000'		
TSC-316-500-35-150	1/2"	150'		
TSC-316-500-35-300	1/2"	300'		
TSC-316-500-35-500	1/2"	500'		
TSC-316-500-35-1000	1/2"	1000'		

COIL - 304SS - WELDED - .035 WALL - DOMESTIC

PART NUMBER	OD	LENGTH	PRICE	LIST
TWC-304-250-35-150D	1/4"	150'		
TWC-304-250-35-300D	1/4"	300'		
TWC-304-250-35-500D	1/4"	500'		
TWC-304-375-35-150D	3/8"	150'		
TWC-304-375-35-300D	3/8"	300'		
TWC-304-375-35-500D	3/8"	500'		
TWC-304-375-35-1000D	3/8"	1000'		
TWC-304-500-35-150D	1/2"	150'		
TWC-304-500-35-300D	1/2"	300'		
TWC-304-500-35-500D	1/2"	500'		
TWC-304-500-35-1000D	1/2"	1000'		

COIL - 316SS - WELDED - .035 WALL - DOMESTIC

PART NUMBER	OD	LENGTH	PRICE	LIST
TWC-316-250-35-150D	1/4"	150'		
TWC-316-250-35-300D	1/4"	300'		
TWC-316-250-35-500D	1/4"	500'		
TWC-316-250-35-1000D	1/4"	1000'		
TWC-316-375-35-150D	3/8"	150'		
TWC-316-375-35-300D	3/8"	300'		
TWC-316-375-35-500D	3/8"	500'		
TWC-316-375-35-1000D	3/8"	1000'		
TWC-316-500-35-150D	1/2"	150'		
TWC-316-500-35-300D	1/2"	300'		
TWC-316-500-35-500D	1/2"	500'		
TWC-316-500-35-1000D	1/2"	1000'		

COIL - 316SS - SEAMLESS - .035 WALL - DOMESTIC

PART NUMBER	OD	LENGTH	PRICE	LIST
TSC-316-250-35-150D	1/4"	150'		
TSC-316-250-35-300D	1/4"	300'		
TSC-316-250-35-500D	1/4"	500'		
TSC-316-250-35-1000D	1/4"	1000'		
TSC-316-375-35-150D	3/8"	150'		
TSC-316-375-35-300D	3/8"	300'		
TSC-316-375-35-500D	3/8"	500'		
TSC-316-375-35-1000D	3/8"	1000'		
TSC-316-500-35-150D	1/2"	150'		
TSC-316-500-35-300D	1/2"	300'		
TSC-316-500-35-500D	1/2"	500'		
TSC-316-500-35-1000D	1/2"	1000'		

Alloys Available: Monel, Inconel, Super Duplex, & More



844-200-MAKO



**BALL VALVES * NEEDLE VALVES * TUBE
 FITTINGS INSTRUMENT FITTINGS * CHECK VALVES
 * RELIEF VALVES * JIC * ULTRA PURE HIGH
 PRESSURE FITTINGS & MORE**

**Total Source for Instrumentation
 & Control Products**

Commodity Product - Prices subject to change

Additional sizes and types available- Call 405-509-2665