

## Catamount® Terminals

### Catamount® Terminals – Now in Convenient, Spillproof, Re-Usable Packaging!

While poly bags keep their contents dry, they don't offer much other protection, and they aren't environmentally friendly. That's why Catamount® terminals now come in sturdy plastic containers that safeguard the connectors inside against crushing and can be re-used or recycled when empty. T&B is always adding value to its products. With the introduction of a durable plastic container, the value of T&B's Catamount® terminals has been significantly enhanced. No more lost or spilled terminals because of inadequate packaging.



Cat. No.	Wire Range	Gros. de boulon	Pkg. Qty.
<b>Vinyl Insulated Ring Terminals</b>			
TV18-6R-XV	22-16	#6	15
TV18-8R-XV		#8	
TV18-10R-XV		#10	
TV14-6R-XV	16-14	#6	15
TV14-8R-XV		#8	
TV14-10R-XV		#10	
TV10-8R-XV	12-10	#8	15
TV10-10R-XV		#10	
TV10-14R-XV		1/4 in.	



Cat. No.	Wire Range	Gros. de boulon	Pkg. Qty.
<b>Vinyl Insulated Fork Terminals</b>			
TV18-6F-XV	22-16	#6	15
TV18-8F-XV		#8	
TV14-6F-XV		#6	
TV14-8F-XV	16-14	#8	15
TV14-10F-XV		#10	
TV10-8F-XV		#8	
TV10-10F-XV	12-10	#10	15
TV10-14F-XV		1/4 in.	



Cat. No.	Wire Range	Pkg. Qty.
<b>Vinyl Insulated Butt Splices</b>		
TV18-BS-XV	22-16	15
TV14-BS-XV	16-14	15
TV10-BS-XV	12-10	15



Cat. No.	Wire Range	Qty	Pkg. Qty.
<b>Vinyl Insulated Butt Splices Kit</b>			
TV10-18-BS	22-18	5	15
	16-14		
	12-10		



Cat. No.	Wire Range	Pkg. Qty.
<b>Nylon Insulated Wire Joints</b>		
TN18-WJ-XV	22-18	15
TN14-WJ-XV	16-14	
TN10-WJ-XV	12-10	



Cat. No.	Wire Range	Pkg. Qty.
<b>Vinyl Insulated Double Crimp Locking Fork</b>		
TV18-10LFD-XV	22-16	15
TV18-6LFD-XV		
TV18-8LFD-XV		
TV14-10LFD-XV	16-14	15
TV14-6LFD-XV		
TV14-8LFD-XV		
TV10-10LFD-XV	12-10	15
TV10-6LFD-XV		
TV10-8LFD-XV		



Cat. No.	Wire Range	Pkg. Qty.
<b>Vinyl Insulated Locking Fork Terminal</b>		
TV18-10LF-XV	22-16	15
TV18-6LF-XV		
TV18-8LF-XV		
TV14-10LF-XV	16-14	15
TV14-6LF-XV		
TV14-8LF-XV		
TV10-10LF-XV	12-10	15
TV10-6LF-XV		
TV10-8LF-XV		



Cat. No.	Wire Range	Pkg. Qty.
<b>Vinyl Insulated Female Disconnects – 250 Series</b>		
TV18-250FD-XV	22-16	15
TV14-250FD-XV	16-14	15
TV10-250FD-XV	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
<b>Vinyl Insulated Male Disconnects – 250 Series</b>		
TV18-250MD-XV	22-16	15
TV14-250MD-XV	16-14	15
TV10-250MD-XV	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
<b>Non insulated Ring Terminals</b>		
T14-10R-XV	16-14	15
T14-8R-XV		
T10-10R-XV	12-10	15
T10-14R-XV		
T10-8R-XV		



Cat. No.	Wire Range	Pkg. Qty.
<b>Non insulated Fork Terminals</b>		
T18-10F-XV	22-18	15
T18-8F-XV		
T14-10F-XV	16-14	15
T14-8F-XV		
T10-10F-XV	12-10	15
T10-14F-XV		
T10-8F-XV		



Cat. No.	Wire Range	Pkg. Qty.
<b>Vinyl Insulated Blade Terminal</b>		
TV18-10BL-XV	22-16	15
TV14-10BL-XV	16-14	15
TV14-18BL-XV		
TV10-10BL-XV	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
<b>Vinyl Insulated Pin Terminal</b>		
TV18-12PT-XV	22-16	15
TV14-12PT-XV	16-14	15
TV10-14PT-XV	12-10	15



## Catamount® Terminals



Cat. No.	Wire Range	Pkg. Qty.
Vinyl Fully Insulated Double Crimp Female Disconnect		
<a href="#">TVF18-250FDD-XV</a>	22-16	15
<a href="#">TVF14-250FDD-XV</a>	16-14	15
<a href="#">TVF10-250FDD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Vinyl Fully Insulated Female Disconnect		
<a href="#">TVF18-250FD-XV</a>	22-16	15
<a href="#">TVF14-250FD-XV</a>	16-14	15
<a href="#">TVF10-250FD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Vinyl Insulated Piggy Back Disconnect		
<a href="#">TV18-250PD-XV</a>	22-16	15
<a href="#">TV14-250PD-XV</a>	16-14	15
<a href="#">TV10-250PD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Vinyl Insulated Double Crimp Piggy Back Disconnect		
<a href="#">TV18-250PDD-XV</a>	22-16	15
<a href="#">TV14-250PDD-XV</a>	16-14	15
<a href="#">TV10-250PDD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Nylon Fully Insulated Female Disconnect		
<a href="#">TNF18-250FD-XV</a>	22-16	15
<a href="#">TNF14-250FD-XV</a>	16-14	15
<a href="#">TNF10-250FD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Nylon Fully Insulated Male Disconnect		
<a href="#">TNF18-250MD-XV</a>	22-16	15
<a href="#">TNF14-250MD-XV</a>	16-14	15
<a href="#">TNF10-250MD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Vinyl Insulated Double Crimp Female Disconnect		
<a href="#">TV18-250FDD-XV</a>	22-16	15
<a href="#">TV14-250FDD-XV</a>	16-14	15
<a href="#">TV10-250FDD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Vinyl Insulated Quick Splice		
<a href="#">TV18-00QS-V</a>	22-18	15
<a href="#">TV14-00QS-V</a>	18-14	15
<a href="#">TV10-00QS-V</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Nylon Fully Insulated Double Crimp Female Disconnects		
<a href="#">TNF18-250FDD-XV</a>	22-16	15
<a href="#">TNF14-250FDD-XV</a>	16-14	15
<a href="#">TNF10-250FDD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Vinyl Insulated Double Crimp Male Disconnect		
<a href="#">TV18-250MDD-XV</a>	22-16	15
<a href="#">TV14-250MDD-XV</a>	16-14	15
<a href="#">TV10-250MDD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Nylon Fully Insulated Female Bullet		
<a href="#">TNF18-4FB-XV</a>	22-16	15
<a href="#">TNF14-4FB-XV</a>	16-14	15



Cat. No.	Wire Range	Pkg. Qty.
Nylon Fully Insulated Male Bullet		
<a href="#">TNF18-4MB-XV</a>	22-16	15
<a href="#">TNF14-4MB-XV</a>	16-14	15



Cat. No.	Wire Range	Pkg. Qty.
Nylon Fully Insulated Double Crimp Male Disconnect		
<a href="#">TNF18-250MDD-XV</a>	22-16	15
<a href="#">TNF14-250MDD-XV</a>	16-14	15
<a href="#">TNF10-250MDD-XV</a>	12-10	15

## Catamount® Terminals

### Catamount® Terminals – Now in Convenient, Spillproof, Re-Usable Packaging!

While poly bags keep their contents dry, they don't offer much other protection, and they aren't environmentally friendly. That's why Catamount® terminals now come in sturdy plastic containers that safeguard the connectors inside against crushing and can be re-used or recycled when empty. T&B is always adding value to its products. With the introduction of a durable plastic container, the value of T&B's Catamount® terminals has been significantly enhanced. No more lost or spilled terminals because of inadequate packaging.



Cat. No.	Wire Range	Gros. de boulon	Pkg. Qty.
<b>Vinyl Insulated Ring Terminals</b>			
TV18-6R-XV	22-16	#6	15
TV18-8R-XV		#8	
TV18-10R-XV		#10	
TV14-6R-XV	16-14	#6	15
TV14-8R-XV		#8	
TV14-10R-XV		#10	
TV10-8R-XV	12-10	#8	15
TV10-10R-XV		#10	
TV10-14R-XV		1/4 in.	



Cat. No.	Wire Range	Gros. de boulon	Pkg. Qty.
<b>Vinyl Insulated Fork Terminals</b>			
TV18-6F-XV	22-16	#6	15
TV18-8F-XV		#8	
TV14-6F-XV		#6	
TV14-8F-XV	16-14	#8	15
TV14-10F-XV		#10	
TV10-8F-XV		#8	
TV10-10F-XV	12-10	#10	15
TV10-14F-XV		1/4 in.	



Cat. No.	Wire Range	Pkg. Qty.
<b>Vinyl Insulated Butt Splices</b>		
TV18-BS-XV	22-16	15
TV14-BS-XV	16-14	15
TV10-BS-XV	12-10	15



Cat. No.	Wire Range	Qty	Pkg. Qty.
<b>Vinyl Insulated Butt Splices Kit</b>			
TV10-18-BS	22-18	5	15
	16-14		
	12-10		



Cat. No.	Wire Range	Pkg. Qty.
<b>Nylon Insulated Wire Joints</b>		
TN18-WJ-XV	22-18	15
TN14-WJ-XV	16-14	
TN10-WJ-XV	12-10	



Cat. No.	Wire Range	Pkg. Qty.
<b>Vinyl Insulated Double Crimp Locking Fork</b>		
TV18-10LFD-XV	22-16	15
TV18-6LFD-XV		
TV18-8LFD-XV		
TV14-10LFD-XV	16-14	15
TV14-6LFD-XV		
TV14-8LFD-XV		
TV10-10LFD-XV	12-10	15
TV10-6LFD-XV		
TV10-8LFD-XV		



Cat. No.	Wire Range	Pkg. Qty.
<b>Vinyl Insulated Locking Fork Terminal</b>		
TV18-10LF-XV	22-16	15
TV18-6LF-XV		
TV18-8LF-XV		
TV14-10LF-XV	16-14	15
TV14-6LF-XV		
TV14-8LF-XV		
TV10-10LF-XV	12-10	15
TV10-6LF-XV		
TV10-8LF-XV		



Cat. No.	Wire Range	Pkg. Qty.
<b>Vinyl Insulated Female Disconnects – 250 Series</b>		
TV18-250FD-XV	22-16	15
TV14-250FD-XV	16-14	15
TV10-250FD-XV	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
<b>Vinyl Insulated Male Disconnects – 250 Series</b>		
TV18-250MD-XV	22-16	15
TV14-250MD-XV	16-14	15
TV10-250MD-XV	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
<b>Non insulated Ring Terminals</b>		
T14-10R-XV	16-14	15
T14-8R-XV		
T10-10R-XV		
T10-14R-XV	12-10	15
T10-8R-XV		



Cat. No.	Wire Range	Pkg. Qty.
<b>Non insulated Fork Terminals</b>		
T18-10F-XV	22-18	15
T18-8F-XV		
T14-10F-XV	16-14	15
T14-8F-XV		
T10-10F-XV	12-10	15
T10-14F-XV		
T10-8F-XV		



Cat. No.	Wire Range	Pkg. Qty.
<b>Vinyl Insulated Blade Terminal</b>		
TV18-10BL-XV	22-16	15
TV14-10BL-XV	16-14	15
TV14-18BL-XV		
TV10-10BL-XV	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
<b>Vinyl Insulated Pin Terminal</b>		
TV18-12PT-XV	22-16	15
TV14-12PT-XV	16-14	15
TV10-14PT-XV	12-10	15



## Catamount® Terminals



Cat. No.	Wire Range	Pkg. Qty.
Vinyl Fully Insulated Double Crimp Female Disconnect		
<a href="#">TVF18-250FDD-XV</a>	22-16	15
<a href="#">TVF14-250FDD-XV</a>	16-14	15
<a href="#">TVF10-250FDD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Vinyl Fully Insulated Female Disconnect		
<a href="#">TVF18-250FD-XV</a>	22-16	15
<a href="#">TVF14-250FD-XV</a>	16-14	15
<a href="#">TVF10-250FD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Vinyl Insulated Piggy Back Disconnect		
<a href="#">TV18-250PD-XV</a>	22-16	15
<a href="#">TV14-250PD-XV</a>	16-14	15
<a href="#">TV10-250PD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Vinyl Insulated Double Crimp Piggy Back Disconnect		
<a href="#">TV18-250PDD-XV</a>	22-16	15
<a href="#">TV14-250PDD-XV</a>	16-14	15
<a href="#">TV10-250PDD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Nylon Fully Insulated Female Disconnect		
<a href="#">TNF18-250FD-XV</a>	22-16	15
<a href="#">TNF14-250FD-XV</a>	16-14	15
<a href="#">TNF10-250FD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Nylon Fully Insulated Male Disconnect		
<a href="#">TNF18-250MD-XV</a>	22-16	15
<a href="#">TNF14-250MD-XV</a>	16-14	15
<a href="#">TNF10-250MD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Vinyl Insulated Double Crimp Female Disconnect		
<a href="#">TV18-250FDD-XV</a>	22-16	15
<a href="#">TV14-250FDD-XV</a>	16-14	15
<a href="#">TV10-250FDD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Vinyl Insulated Quick Splice		
<a href="#">TV18-00QS-V</a>	22-18	15
<a href="#">TV14-00QS-V</a>	18-14	15
<a href="#">TV10-00QS-V</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Nylon Fully Insulated Double Crimp Female Disconnects		
<a href="#">TNF18-250FDD-XV</a>	22-16	15
<a href="#">TNF14-250FDD-XV</a>	16-14	15
<a href="#">TNF10-250FDD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Vinyl Insulated Double Crimp Male Disconnect		
<a href="#">TV18-250MDD-XV</a>	22-16	15
<a href="#">TV14-250MDD-XV</a>	16-14	15
<a href="#">TV10-250MDD-XV</a>	12-10	15



Cat. No.	Wire Range	Pkg. Qty.
Nylon Fully Insulated Female Bullet		
<a href="#">TNF18-4FB-XV</a>	22-16	15
<a href="#">TNF14-4FB-XV</a>	16-14	15



Cat. No.	Wire Range	Pkg. Qty.
Nylon Fully Insulated Male Bullet		
<a href="#">TNF18-4MB-XV</a>	22-16	15
<a href="#">TNF14-4MB-XV</a>	16-14	15



Cat. No.	Wire Range	Pkg. Qty.
Nylon Fully Insulated Double Crimp Male Disconnect		
<a href="#">TNF18-250MDD-XV</a>	22-16	15
<a href="#">TNF14-250MDD-XV</a>	16-14	15
<a href="#">TNF10-250MDD-XV</a>	12-10	15