



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

TY26M 11.08" Ty-Rap (Bulk)

Abb Installation Products, Inc

Catalog Number	TY26M
Manufacturer	Abb Installation Products, Inc
Description	Cable Tie, Natural Polyamide (Nylon 6.6) For Temperatures Up to 85 Degrees Celsius (185 F) For Indoor Applications, UI/En/CSA62275 Type 2/21 Rated For Ah-2 Plenum, Length Of 281.94MM (11.1 Inches), Width Of 3.6MM (0.14 Inches), Tensile Strength Rating Of 133.4 Newtons (30 Pounds), Bulk Pack
Weight per unit	0.0030 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	40:180
------------------	--------

Dimensions and Weight

Length	10.9
Thickness	0.04
Width	0.14

Descriptions

Description	11.08" TY-RAP (BULK)
extra long description	ABB TY26M CABLE TIE 30LB 11.1IN NAT
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 281.94mm (11.1 Inches), Width of 3.6mm (0.14 Inches), Tensile Strength Rating of 133.4 Newtons (30 Pounds), Bulk Pack
Product Type	Cable Tie 30LB 11.1IN Natural Nylon
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210824680
Manufacturers Part Number	TY26M
UPC	786210824680

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 1000

Packaging

Carton 1000

Package 10000

Weight Per each 0.003

Uses, Certifications, and Standards

standard UL E49405