




# T&B Fittings

**NOTES:**

1. ALL CONDUIT TO BE ORANGE IN COLOR UNLESS OTHERWISE SPECIFIED
2. CONDUIT TO HAVE BRAIDED NYLON MESH LAYERED BETWEEN PVC JACKETS
3. ALL CONDUIT TO BE RATED -20° TO 60°C



TYPEA200-50	2" TYPE A CONDUIT	50	2.045/2.080	2.605/2.640
TYPEA150-50	1-1/2" TYPE A CONDUIT	50	1.585/1.620	2.045/2.080
TYPEA125-100	1-1/4" TYPE A CONDUIT	100	1.370/1.395	1.800/1.825
TYPEA100-100	1" TYPE A CONDUIT	100	1.030/1.395	1.415/1.440
TYPEA75-500	3/4" TYPE A CONDUIT	500	.818/.835	1.150/1.170
TYPEA75-175	3/4" TYPE A CONDUIT	175	.818/.835	1.150/1.170
TYPEA50-500	1/2" TYPE A CONDUIT	500	.620/.640	.910/.930
TYPEA50-200	1/2" TYPE A CONDUIT	200	.620/.640	.910/.930
TYPEA38-250	3/8" TYPE A CONDUIT	250	.485/.505	.755/.775
CAT #	DESCRIPTION	LENGTH (FT)	INSIDE DIA (IN)	OUTSIDE DIA (IN)

**GENERAL NOTES**

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [ ] ARE IN METRIC UNITS.

**Thomas & Betts**  
A Member of the ABB Group

www.tnb.com

**REVISIONS**

1	SEE ERN ( 2015344 ) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: RM401883
---	---

**DESCRIPTION: TYPE A NONMETALLIC CONDUIT**

ORIGINAL PROJECT NO / ( ERN NO )	SHEET NO:	REV. NO:	DRAWING NO:
<b>RD55635 / ( 2005658 )</b>	<b>1 OF 1</b>	<b>1</b>	<b>WSD-000172</b>