



## Catalog No. U054

**Description:** 50A SURFACE UNMTRD

**UPC No** 784567300185

**Home > Power Outlets > Power Outlets**



Representative Image

Midwest Electric's Temporary Power and Power Outlets are a means of providing power required by various construction trades, residential sites, and mobile electrical applications. Temporary Power and Power Outlets offer one or more receptacles, with or without overcurrent protection, disconnecting, metering, and/or pedestal mounting functions, in a single enclosure of G-90 zinc-coated steel. The NEMA 3R rainproof enclosure is lockable and engineered to provide maximum protection against weather, vandalism, and normal field use.

### Descriptors

Category	Power Outlets
----------	---------------

### Specifications

Mounting	Surface
Heads	1
Metering	Unmetered
Receptacles	14-50R
Feed	Overhead
AIC	10,000
Amps	50
Cabinet Size	5 in. W X 7 in. H
Circuit Protection	No
Hub Provision	Yes
Installed Breaker	None
Load Center	FR67
Loop Feed	No
Phase	1
Suitable for Service Equipment	No
Unit Weight	9 lb
Volts	120/240

### Classifications

Standard Package	4
Stock Class Code	Stock

### Approvals

Certification	UL/CUL
---------------	--------

## Publications

Title	Publication No.	Publication Type
<a href="#">Storm Season Brochure</a> This brochure highlights the most popular products sold during storm season.	MET1005	Brochures
<a href="#">Storm Season Brochure</a> This brochure highlights the most popular products sold during storm season.	005	Brochures
<a href="#">Durable Outdoor Power Outlets</a> power the great outdoors!	MET-007A	Brochures
<a href="#">Heavy Duty Power Outlets</a> 2 pages. MET-020 Rev. B.	MET-020A	Brochures

**Additional Documentation:** Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.