

Specifications



Photo is representative

Eaton UASTS61C224CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, Six-jaw, 1-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UASTS61C224CH
UPC	786685216386
PRODUCT LENGTH/DEPTH	4.359 in
PRODUCT HEIGHT	20 in
PRODUCT WIDTH	12 in
PRODUCT WEIGHT	15 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Instrument rated socket
AMPERAGE RATING	20A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Six-jaw
PHASE	Single-phase
ENCLOSURE MATERIAL	Aluminum
NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
ACCESSORIES	Factory wired test switch
NUMBER OF SOCKETS	1

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - UASTS61C224CH](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton UASTS61C224CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, Six-jaw, 1-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UASTS61C224CH
UPC	786685216386
PRODUCT LENGTH/DEPTH	4.359 in
PRODUCT HEIGHT	20 in
PRODUCT WIDTH	12 in
PRODUCT WEIGHT	15 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Instrument rated socket
AMPERAGE RATING	20A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Six-jaw
PHASE	Single-phase
ENCLOSURE MATERIAL	Aluminum
NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
ACCESSORIES	Factory wired test switch
NUMBER OF SOCKETS	1

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - UASTS61C224CH](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

