

Eaton UAT6R2392UUFLCH

Catalog Number: UAT6R2392UUFLCH

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, (2) #1/0-500 kcmil, 4-jaw, 1-ph, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

General specifications



Product Name

Eaton meter socket

UPC

782116997855

Product Height

5.375 in

Product Weight

72 lb

Certifications

UL Listed

Catalog Number

UAT6R2392UUFLCH

Product Length/Depth

14.125 in

Product Width

62.937 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

FMG approved

defaultTaxonomyAttributeLabel

Type

Multiple position residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

Line

#1/0-500 kcmil

Load

#8-250 kcmil

Enclosure material

Aluminum

Number of wires

Three-wire

Connection

Ground connection

Security

Ringless

Voltage rating

600 V

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - SKT/5 GANG 200A 1P (2)HCP

Specifications and datasheets

Eaton Specification Sheet - UAT6R2392UUFLCH

Number of sockets

6



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton UAT6R2392UUFLCH

Catalog Number: UAT6R2392UUFLCH

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, (2) #1/0-500 kcmil, 4-jaw, 1-ph, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

General specifications



Product Name

Eaton meter socket

UPC

782116997855

Product Height

5.375 in

Product Weight

72 lb

Certifications

UL Listed

Catalog Number

UAT6R2392UUFLCH

Product Length/Depth

14.125 in

Product Width

62.937 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

FMG approved

defaultTaxonomyAttributeLabel

Type

Multiple position residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

Line

#1/0-500 kcmil

Load

#8-250 kcmil

Enclosure material

Aluminum

Number of wires

Three-wire

Connection

Ground connection

Security

Ringless

Voltage rating

600 V

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - SKT/5 GANG 200A 1P (2)HCP

Specifications and datasheets

Eaton Specification Sheet - UAT6R2392UUFLCH

Number of sockets

6



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia