

Eaton UATRS101CCH

Catalog Number: UATRS101CCH

Eaton meter socket, 1-pos resi service, 125A, Over/under, Small hub closing plate mounted, #8-2/0 AWG, 4-jaw, 1-ph, #8-2/0 AWG, none, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UATRS101CCH

UPC

786685181219

Product Length/Depth

3.5 in

Product Height

10.87 in

Product Width

8 in

Product Weight

7 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Catalog Notes

Iowa approved



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Type

Single-position residential service

Amperage Rating

125A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Line

#8-2/0 AWG

Load

#8-2/0 AWG

Enclosure material

Aluminum

Number of wires

Three-wire

Hub type

3-5/16 in hub opening plate

Security

Ringless

Voltage rating

600 V

Number of sockets

1

Resources

Brochures

Single Meter Sockets

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - SKT 125A 1P HCP

Specifications and datasheets

Metering Equipment - Utilities Servicing Upstate New York

Eaton Specification Sheet - UATRS101CCH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)