

COOPER LIGHTING - METALUX®

DESCRIPTION

The Metalux Electronic Undercabinet Series provides an efficient task lighting solution for any decor. Available in either the Ultra Slim profile with T5 lamp technology or Slim profile with T8 lamps. The electronic undercabinet series is not only high quality but an excellent value with post-painted housings, 100% acrylic non-yellowing lenses, and color corrected lamps. Available in various lengths, the undercabinet fixture conforms to various applications such as kitchens, offices, study areas, displays, computer stations and any other application where an inconspicuous light source is required.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Construction

Thin profile housing constructed of heavy gauge cold rolled steel. Housing features rounded corners and no exposed fasteners. Keyhole mounting slots are located on top of housing for ease of installation.

Electrical*

Energy-Star qualified 120v Electronic instant-start ballast for quiet operation. All units ship with 3000k lamps standard. All fixtures shipped direct wired. Rocker switch (included) can be field installed. UL listed for damp locations.

Finish

Standard with white finish applied after fabrication.

Shielding


Non-yellowing acrylic diffuser snaps into housing for easy relamping and maintenance.



T5



T8



Catalog Number	Length	Width	Depth
UC12T518	12-1/4"	5"	1-3/8"
UC21T5113	21-1/4"	5"	1-3/8"
UC24T528	24-1/2"	5"	1-3/8"
UC33T51813	33-3/8"	5"	1-3/8"
UC42T5213	42-1/2"	5"	1-3/8"
UC18T8115	18-1/4"	3-7/8"	1-5/8"
UC24T8117	24-1/4"	3-7/8"	1-5/8"
UC36T8125	36-1/8"	3-7/8"	1-5/8"
UC48T8132	48-1/6"	3-7/8"	1-5/8"

Electronic Undercabinet Series

1 OR 2 LAMP

Low Profile Undercabinet Series



Catalog Number	Description
UC12T518	12", 1 lamp T5, 8 watt, 120v, electronic ballast, lamp included
UC21T5113	21", 1 lamp T5, 13 watt, 120v, electronic ballast, lamp included
UC24T528	24", 2 lamp T5, 2/8 watt, 120v, electronic ballast, lamps included
UC33T51813	33", 2 lamp T5, 8+13 watt, 120v, electronic ballast, lamps included
UC42T5213	42", 2 lamp T5, (2) 13 watt, 120v, electronic ballast, lamps included
UC18T8115	18", 1 lamp T8, 15 watt, 120v, electronic ballast, lamp included
UC24T8117	24", 1 lamp T8, 17 watt, 120v, electronic ballast, lamp included
UC36T8125	36", 1 lamp T8, 25 watt, 120v, electronic ballast, lamp included
UC48T8132	48", 1 lamp T8, 32 watt, 120v, electronic ballast, lamp included

ENERGY DATA

Input Watts:

EB Ballast & STD Lamps

108T5 (9)
113T5 (14)
108113T5 (23)
208T5 (19)
213T5 (27)
115T8 (20)
117T8 (22)
125T8 (28)
132T8 (32)

*Reference the lamp/ballast data in the Technical Section for specific lamp/ballast requirements.

LAMPS CONTAIN MERCURY. DISPOSE ACCORDING TO LOCAL, STATE OR FEDERAL LAWS

