

Eaton UGHTRS213CE

Catalog Number: UGHTRS213CE

Eaton meter socket, 1-pos resi service, 200A, Over/under, Hub cover plate, #6-350 kcmil, 5-jaw, 1-ph, #6-350 kcmil, Horn bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, Gnded 5th terminal (9 o'clock position), 600 Vac

General specifications



Product Name

Eaton meter socket

UPC

786685217918

Product Height

15.13 in

Product Weight

13 lb

Certifications

UL Listed

Catalog Number

UGHTRS213CE

Product Length/Depth

4.5 in

Product Width

11.25 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

defaultTaxonomyAttributeLabel

Type

Single-position residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Five-jaw

Phase

Single-phase

Ground

Triplex

Terminals

Grounded fifth terminal (9 o'clock position)

Utility approvals

WI : Madison Gas and Electric (MGE)

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Three-wire

Hub type

Hub cover plate

Security

Ringless

Voltage rating

600 V

Bypass

Horn

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - METER SOCKET UHTRS2139\(X\)E, UGHTRS213\(X\)E 200AMP, 1 Ø OH/UG, HORN BYPASS RINGLESS STYLE, HBP](#)

Specifications and datasheets

[Eaton Specification Sheet - UGHTRS213CE](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton UGHTRS213CE

Catalog Number: UGHTRS213CE

Eaton meter socket, 1-pos resi service, 200A, Over/under, Hub cover plate, #6-350 kcmil, 5-jaw, 1-ph, #6-350 kcmil, Horn bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, Gnded 5th terminal (9 o'clock position), 600 Vac

General specifications



Product Name

Eaton meter socket

UPC

786685217918

Product Height

15.13 in

Product Weight

13 lb

Certifications

UL Listed

Catalog Number

UGHTRS213CE

Product Length/Depth

4.5 in

Product Width

11.25 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

defaultTaxonomyAttributeLabel

Type

Single-position residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Five-jaw

Phase

Single-phase

Ground

Triplex

Terminals

Grounded fifth terminal (9 o'clock position)

Utility approvals

WI : Madison Gas and Electric (MGE)

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Three-wire

Hub type

Hub cover plate

Security

Ringless

Voltage rating

600 V

Bypass

Horn

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - METER SOCKET UHTRS2139\(X\)E, UGHTRS213\(X\)E 200AMP, 1 Ø OH/UG, HORN BYPASS RINGLESS STYLE, HBP](#)

Specifications and datasheets

[Eaton Specification Sheet - UGHTRS213CE](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia