



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UGP20231QW 5-20P 20A 125V PLG Hubbell--Killark

Catalog Number	UGP20231QW
Manufacturer	Hubbell--Killark
Description	Ugp Series - Aluminum 20 Amp 125VAC Interchangeable Blade Style Plug With Quick Wiring - Nema Configuration 5-20P
Weight per unit	0.4000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	20
Cord Type	S, SO, ST, STO, SOO, SOW, or SOOW
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Number of Wires	3
Phase	1
Poles	2
Receptacle Type	Delayed Action
Voltage Rating	125 VAC
Wire Size	10 , 12 , or 14

Dimensions and Weight

Size	6.625 in x 2.375 in x 1.875 in
------	--------------------------------

Descriptions

Description	5-20P 20A 125V PLG
extra long description	KLRK UGP-20231QW 20A PLUG 5-20P QUI
Long Description	UGP Series - Aluminum 20 Amp 125VAC Interchangeable Blade Style Plug With Quick Wiring - NEMA Configuration 5-20P
Product Type	20A Plug 5-20P Quick Wire
Special Features	ACCEPTOR plugs conform to NEMA configurations and can be used with standard receptacles in non-hazardous areas to maximize equipment utilization. The system's "turn to engage" feature locks in plug and can be used to prevent accidental disengagement of cr

Manufacturer Information

Brand	KILLARK
GTIN	00783936076669
Manufacturers Part Number	UGP-20231QW
series	UGP
UPC	783936076669



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Straight Blade

Packaging

Carton	1
Weight Per each	0.4

Uses, Certifications, and Standards

Application	Petroleum refineries, chemical plants, wet/damp areas, corrosive environments, petroleum plants, grain elevators/feed mills, flour and feed mills, and indoor or outdoor locations
environmental conditions	Wet and hazardous locations
nema rating	3, 4, 4X
standard	UL, CSA