



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## UGP20232QW 6-20P 20A 250V PLG Hubbell--Killark

Catalog Number	UGP20232QW
Manufacturer	Hubbell--Killark
Description	Ugp Series - Aluminum 20 Amp 250VAC Interchangeable Blade Style Plug With Quick Wiring - Nema Configuration 6-20P
Weight per unit	0.4000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	20
Cord Type	S, SO, ST, STO, SOO, SOW, or SOOW
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Number of Wires	3
Phase	1
Poles	2
Receptacle Type	Delayed Action
Voltage Rating	250 VAC
Wire Size	10 , 12 , or 14

### Dimensions and Weight

Size	6.625 in x 2.375 in x 1.875 in
------	--------------------------------

### Descriptions

Description	6-20P 20A 250V PLG
extra long description	KLRK UGP-20232QW 20A PLUG 6-20P QUI
Long Description	UGP Series - Aluminum 20 Amp 250VAC Interchangeable Blade Style Plug With Quick Wiring - NEMA Configuration 6-20P
Product Type	20A Plug 6-20P Quick Wire
Special Features	ACCEPTOR plugs conform to NEMA configurations and can be used with standard receptacles in non-hazardous areas to maximize equipment utilization. The system's "turn to engage" feature locks in plug and can be used to prevent accidental disengagement of cr

### Manufacturer Information

Brand	KILLARK
GTIN	00783936076676
Manufacturers Part Number	UGP-20232QW
series	UGP
UPC	783936076676



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Straight Blade

## Packaging

Carton	1
Weight Per each	0.4

## Uses, Certifications, and Standards

Application	Petroleum refineries, chemical plants, wet/damp areas, corrosive environments, petroleum plants, grain elevators/feed mills, flour and feed mills, and indoor or outdoor locations
environmental conditions	Wet and hazardous locations
nema rating	3, 4, 4X
standard	UL, CSA