



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UNF605 2" Female Union

Crouse-Hinds

Catalog Number	UNF605
Manufacturer	Crouse-Hinds
Description	Union, 2 In Trade Size, Unf Model, Straight, Electro Galvanized With Chromate Treatment, Female Connection, 2-9/16 In Length, 3-13/16 In Diameter, 3.38 LB
Weight per unit	3.4 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Threaded
dimensions	2.6900 IN X 3.8800 IN X 3.8800 IN

Descriptions

Description	2" FEMALE UNION
extra long description	CRS-H UNF605 2 NPT FEMALE UNF UNION
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit

Manufacturer Information

Brand	Eaton
GTIN	00782274644400
UPC	782274644400

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Union

Packaging

Carton	1
Package	2
Weight Per each	3.38

Uses, Certifications, and Standards

Enclosure	Class I Div 1 2 Group A B C D, Class II Div 1 Group E F G, Class II Div 2 Group F G, Class III
standard	UL 886, CSA C22.2