

Eaton UNRRS101BEUSE

Catalog Number: UNRRS101BEUSE

Eaton meter socket, 3-5/16 Hub Opening, 125A, Overhead, 3-5/16 Hub Opening, #8-2/0 kcmil, Four-jaw, Single-phase, #8-2/0 kcmil, Sockets:1, Three-wire, Ring, 600V



General specifications

Product Name

Eaton meter socket

Catalog Number

UNRRS101BEUSE

UPC

786685217840

Product Length/Depth

3.6 in

Product Height

11.05 in

Product Width

8.22 in

Product Weight

7.35 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

3-5/16 Hub Opening

Amperage Rating

125A

Feed type

Overhead

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

TX : CenterPoint Energy (HL&P/Reliant)

Line

#8-2/0 kcmil

Load

#8-2/0 kcmil

Enclosure material

16 GA GALV STEEL

Number of wires

Three-wire

Hub type

3-5/16 hub opening

Security

Ring

Voltage rating

600 V

Number of sockets

1

Resources

Brochures

Single Meter Sockets

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER SOCKET URTRS101(X)E, UNRRSS101(X)E
125AMP, 1 ø OH/UG, RINGTYPE

Specifications and datasheets

Eaton Specification Sheet - UNRRS101BEUSE



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton UNRRS101BEUSE

Catalog Number: UNRRS101BEUSE

Eaton meter socket, 3-5/16 Hub Opening, 125A, Overhead, 3-5/16 Hub Opening, #8-2/0 kcmil, Four-jaw, Single-phase, #8-2/0 kcmil, Sockets:1, Three-wire, Ring, 600V

General specifications



Product Name

Eaton meter socket

Catalog Number

UNRRS101BEUSE

UPC

786685217840

Product Length/Depth

3.6 in

Product Height

11.05 in

Product Width

8.22 in

Product Weight

7.35 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

3-5/16 Hub Opening

Amperage Rating

125A

Feed type

Overhead

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

TX : CenterPoint Energy (HL&P/Reliant)

Line

#8-2/0 kcmil

Load

#8-2/0 kcmil

Enclosure material

16 GA GALV STEEL

Number of wires

Three-wire

Hub type

3-5/16 hub opening

Security

Ring

Voltage rating

600 V

Number of sockets

1

Resources

Brochures

Single Meter Sockets

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER SOCKET URTRS101(X)E, UNRRSS101(X)E
125AMP, 1 ø OH/UG, RINGTYPE

Specifications and datasheets

Eaton Specification Sheet - UNRRS101BEUSE



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)