

Specifications



Eaton UNRRS213BEUSE

Eaton meter socket, 3 5/16 in hub opening, 200A, Overhead, Hub opening, #6-350 kcmil, Four-jaw, Single-phase, #6-350 kcmil, Sockets:1, Three-wire, Ring, 600V

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UNRRS213BEUSE
UPC	786685217888
PRODUCT LENGTH/DEPTH	4.48 in
PRODUCT HEIGHT	15.11 in
PRODUCT WIDTH	11.22 in
PRODUCT WEIGHT	18 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	3 5/16 in hub opening
AMPERAGE RATING	200A
FEED TYPE	Overhead
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	TX : CenterPoint Energy (HL&P/Reliant)
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
ENCLOSURE MATERIAL	16 GA GALV STEEL
NUMBER OF WIRES	Three-wire
HUB TYPE	Hub opening
SECURITY	Ring
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UNRRS213BEUSE

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

