



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UNY405SA 1-1/4" Male Union

Crouse-Hinds

Catalog Number	UNY405SA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Uny Union, Rigid/Imc, Male, Copper-Free Aluminum, 1-1/4"
Weight per unit	0.6900 (lbs/each)
Product Category	Aluminum

Features

connection	Threaded
dimensions	3.6300 IN X 2.7500 IN X 2.7500 IN

Descriptions

Description	1-1/4" MALE UNION
extra long description	CRS-H UNY405 SA 1 1/4 NPT MALE UNY
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit
Long Description	Eaton Crouse-Hinds series UNY union, Rigid/IMC, Male, Copper-free aluminum, 1-1/4"
Product Type	1 1/4 NPT Male Uny Al Union
Special Features	2-3/4 In Diameter X 3-3/16 In Length

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274101972
Manufacturers Part Number	UNY405 SA
UPC	782274101972

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Union

Packaging

Carton	1
Package	5
Weight Per each	0.69



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group A B C D, Class II Div 1 Group E F G, Class II
	Div 2 Group F G, Class III
standard	UL 886, CSA C22.2