



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UNY905 3-1/2" Male Union *Crouse-Hinds*

Catalog Number	UNY905
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Uny Union, Rigid/Imc, Male, Feraloy Iron Alloy, Group B Rated, 3-1/2"
Weight per unit	10.7 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Male Threaded, Male Threaded
dimensions	6.5600 IN X 5.6900 IN X 5.6900 IN

Descriptions

Description	3-1/2" MALE UNION
extra long description	CRS-H UNY905 3 1/2 NPT MALE UNY UNI
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit
Long Description	Eaton Crouse-Hinds series UNY union, Rigid/IMC, Male, Feraloy iron alloy, Group B rated, 3-1/2"
Product Type	3 1/2 NPT Male Uny Union
Special Features	5-11/16 In Diameter X 5-1/2 In Length

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274648705
Manufacturers Part Number	UNY905
UPC	782274648705

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Union

Packaging

Carton	1
Weight Per each	10.7



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group B C D, Class II Div 1 Group E F G, Class II Div 2 Group F G, Class III
standard	UL 886, CSA C22.2