



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



URD4040401500 4/0-4/0-4/0 Urd Monmouth Alu 1500'

King Wire Inc.

| | |
|------------------|---|
| Catalog Number | URD4040401500 |
| Manufacturer | King Wire Inc. |
| Description | Type MC Cable, Flame Retardant;Sunlight Resistant Additional Information, Wet/Dry and Interior Wiring Application, Aluminum Alloy Conductor Material, 4/0-4/0-4/0 Awg Conductor Size, 205 A Current Rating, Polyethylene Insulation Material, Metal Free Polyvinyl Chloride (PVC) Jacket Material, Made In Usa, +90 °C Maximum Operating Temperature, 19 (Phase) - Conductors, 0.857 X 1.445 In Outside Diameter, Strand Solid/Strand, Directive 2002/95/Ec;Federal Specification JC-30B Nec;Nec Nfpa 70, 2011 Edition;Rohs Com |
| Weight per unit | 0.8300 (lbs/ft) |
| Product Category | Seu |

Descriptions

| | |
|-------------|------------------------------------|
| Description | 4/0-4/0-4/0 URD MONMOUTH ALU 1500' |
|-------------|------------------------------------|

Manufacturer Information

| | |
|-------|----------|
| Brand | Aluminum |
|-------|----------|

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Direct Burial Wire |
|----------------------|--------------------|

Availability

| | |
|-------------|------|
| minimum qty | 1500 |
|-------------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1500 |
| Weight Per foot | 0.83 |