

Eaton URS101BCH

Catalog Number: URS101BCH

Eaton meter socket, 1-pos resi service, 125A, Over, 3-5/16 inch hub open, #8-2/0 AWG, 4-jaw, 1-ph, #8-2/0 AWG, Three-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

URS101BCH

UPC

782114003985

Product Length/Depth

3.5 in

Product Height

10.88 in

Product Width

8 in

Product Weight

7 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Catalog Notes

Suitable for either top or bottom service cable entry, Iowa approved

defaultTaxonomyAttributeLabel

Type

Single-position residential service

Amperage Rating

125A

Feed type

Overhead

Number of jaws

Four-jaw

Phase

Single-phase

Line

#8-2/0 AWG

Load

#8-2/0 AWG

Number of wires

Three-wire

Hub type

3-5/16 in hub opening

Security

Ringless

Voltage rating

600 V

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - SKT 125A 1P HO](#)

Specifications and datasheets

[Eaton Specification Sheet - URS101BCH](#)

[Metering Equipment - Utilities Servicing Upstate New York](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)