

# Straight Blade Devices

## 15A, 125V, 2 Pole, 3 Wire Grounding

### USB Charger Receptacles

# HUBBELL

#### Features

- High Power 5 Amp, 5 Volt USB Output
- Two Type C USB Ports
- Tamper Resistant Commercial Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

#### Ordering Information

Description	Color	UPC Number	Catalog Number
Tamper Resistant 15A/125V Duplex, 5 Amp, 5 Volts USB Ports	White	883778307454	USB15C5W

#### Listings


cULus Listed to UL498, UL1310

#### Specifications

Face	RTP
Base	RTP
LED	Green Indicator
Contacts	Plated Steel
Clamp	Plated Steel
Terminal Screws	Plated Steel
Mounting Strap	.040" Zinc Plated Steel
Mounting Screws	Zinc Plated Steel
USB Port	Stainless Steel

#### Performance

<b>Electrical</b>	
Current Interruption	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum Complies with USB BC1.2 Battery Charging and 3.0 Power Delivery Specifications
<b>Mechanical</b>	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
USB Ports	Stainless steel rated for 10,000 plug insertions and removal
<b>Environmental</b>	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C, minimum -40°C (w/o impact)



15A STANDARD  
GRADE DEVICE

#### Online Resources

eCatalog

# Straight Blade Devices

## 15A, 125V, 2 Pole, 3 Wire Grounding

### USB Charger Receptacles

# HUBBELL

#### Features

- High Power 5 Amp, 5 Volt USB Output
- Two Type C USB Ports
- Tamper Resistant Commercial Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

#### Ordering Information


Description	Color	UPC Number	Catalog Number
Tamper Resistant 15A/125V Duplex, 5 Amp, 5 Volts USB Ports	White	883778307454	USB15C5W

#### Listings

cULus Listed to UL498, UL1310

#### Specifications

Face	RTP
Base	RTP
LED	Green Indicator
Contacts	Plated Steel
Clamp	Plated Steel
Terminal Screws	Plated Steel
Mounting Strap	.040" Zinc Plated Steel
Mounting Screws	Zinc Plated Steel
USB Port	Stainless Steel



15A STANDARD  
GRADE DEVICE

#### Online Resources

eCatalog

#### Performance

<b>Electrical</b>	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum Complies with USB BC1.2 Battery Charging and 3.0 Power Delivery Specifications
<b>Mechanical</b>	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
USB Ports	Stainless steel rated for 10,000 plug insertions and removal
<b>Environmental</b>	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C, minimum -40°C (w/o impact)