

Eaton UTH7330UCH

Catalog Number: UTH7330UCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, 5x5 inch hub cover plate, 3/8 inch stud, 7-jaw, three-phase, 3/8 inch stud, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UTH7330UCH

UPC

782116016686

Product Length/Depth

6.5 in

Product Height

39.88 in

Product Width

20 in

Product Weight

60 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Single-position commercial or residential service

Amperage Rating

320A

Feed type

Top/bottom

Number of jaws

Seven-jaw

Phase

Three-phase

Utility approvals

ME : Central Maine Power

NM : El Paso Electric

TX : El Paso Electric

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

KY : Louisville Gas & Electric/Kentucky Utilities

TN : Middle Tennessee EMC

Line

3/8 in stud

Load

3/8 in stud

Number of wires

Four-wire

Hub type

5 x 5 hub cover plate

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Specifications and datasheets

[Eaton Specification Sheet - UTH7330UCH](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton UTH7330UCH

Catalog Number: UTH7330UCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, 5x5 inch hub cover plate, 3/8 inch stud, 7-jaw, three-phase, 3/8 inch stud, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac



General specifications

Product Name	Catalog Number
Eaton meter socket	UTH7330UCH
UPC	Product Length/Depth
782116016686	6.5 in
Product Height	Product Width
39.88 in	20 in
Product Weight	Warranty
60 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Single-position commercial or residential service

Amperage Rating

320A

Feed type

Top/bottom

Number of jaws

Seven-jaw

Phase

Three-phase

Utility approvals

ME : Central Maine Power

NM : El Paso Electric

TX : El Paso Electric

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

KY : Louisville Gas & Electric/Kentucky Utilities

TN : Middle Tennessee EMC

Line

3/8 in stud

Load

3/8 in stud

Number of wires

Four-wire

Hub type

5 x 5 hub cover plate

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Specifications and datasheets

[Eaton Specification Sheet - UTH7330UCH](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)