

# Eaton V2LM2CA2/UNV1

Catalog Number: V2LM2CA2/UNV1

Eaton Crouse-Hinds series Vaporgard V2L LED, 0.12A, Cool white, AC drive, 50W HID or 150-200W incan equiv, 50/60 Hz, Without guard, Heat and impact resistant glass lens, 1700 lm, Copper-free alum, Pend mt, 3/4", 120-277 Vac, 14W

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Vaporgard V2L LED light fixture	V2LM2CA2/UNV1
	UPC
	662276840249
Product Length/Depth	Product Height
8.75 in	4.69 in
Product Width	Product Weight
8.75 in	5.7 lb

## Resources

### Brochures

[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds series Vaporgard V2L/V3L LED brochure](#)

### Catalogs

[Crouse-Hinds series Vaporgard V2L/V3L LED catalog page](#)

### Certification reports

[Vaporgard V2L Hazardous Area LED Light Fixtures UL certification](#)

[Vaporgard V2L Hazardous Area LED Light Fixtures Canadian certification](#)

### Installation instructions

[IF 1636 - Vaporgard V2L LED](#)

[IF 1885 - Vaporgard V2L/V3L Driver Modules - AC Version](#)

### Specifications and datasheets

[Eaton Specification Sheet - V2LM2CA2/UNV1](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)