

# Eaton V48M28T15

Catalog Number: V48M28T15

Eaton general purpose ventilated transformer, Dry Type Distribution, DT-3, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 150°C, 15 kVA, Al windings, Frame: 912B, uses WS38



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose ventilated transformer	V48M28T15
	<b>UPC</b>
	786680035234
<b>Product Length/Depth</b>	<b>Product Height</b>
16.5 in	32.02 in
<b>Product Width</b>	<b>Product Weight</b>
23 in	181 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Physical Attributes

### Coil material

Aluminum

### Design

DT-3

### Frame

912B

### Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

### Type

Dry Type Distribution Transformer

## Performance Ratings

### Frequency rating

60 Hz

### Kva Rating

15 kVA

### Primary voltage

480 V

### Secondary Voltage

208Y/120 V

### Temperature rise

150 °C rise

## Miscellaneous

### Weathershield

WS38

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - V48M28T15](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton V48M28T15

Catalog Number: V48M28T15

Eaton general purpose ventilated transformer, Dry Type Distribution, DT-3, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 150°C, 15 kVA, Al windings, Frame: 912B, uses WS38



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose ventilated transformer	V48M28T15
	<b>UPC</b>
	786680035234
<b>Product Length/Depth</b>	<b>Product Height</b>
16.5 in	32.02 in
<b>Product Width</b>	<b>Product Weight</b>
23 in	181 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Physical Attributes

### Coil material

Aluminum

### Design

DT-3

### Frame

912B

### Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

### Type

Dry Type Distribution Transformer

## Performance Ratings

### Frequency rating

60 Hz

### Kva Rating

15 kVA

### Primary voltage

480 V

### Secondary Voltage

208Y/120 V

### Temperature rise

150 °C rise

## Miscellaneous

### Weathershield

WS38

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - V48M28T15](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)