

Eaton V48M28T15

Catalog Number: V48M28T15

Eaton general purpose ventilated transformer, Dry Type Distribution, DT-3, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 150°C, 15 kVA, Al windings, Frame: 912B, uses WS38



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48M28T15
	UPC
	786680035234
Product Length/Depth	Product Height
16.5 in	32.02 in
Product Width	Product Weight
23 in	181 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

DT-3

Frame

912B

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

15 kVA

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

150 °C rise

Miscellaneous

Weathershield

WS38

Resources

Specifications and datasheets

[Eaton Specification Sheet - V48M28T15](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)