



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## V4ICW 4 Ic New Construction Housing

*Lithonia Lighting - Acuity*

Catalog Number	V4ICW
Manufacturer	Lithonia Lighting - Acuity
Description	This Ic Air-Loc Housing Has A Floating Medium Base Porcelain Socket With Nickel-Plated Copper Screw Shell. It Is Shipped With A Socket Cap to Protect Against Paint Overspray. The Air-Loc Housing Stops Infiltration and Exfiltration Of Air, Reducing Heating and Cooling Costs.
Weight per unit	2.7 (lbs/each)
Product Category	Halogen & Quartz Recessed Arch

### Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	Round

### Dimensions and Weight

Height	8
Length	14
Width	12

### Descriptions

Construction	New Construction
Description	4IN LT FX HOUSING
extra long description	LITH V4IC W VuLite 4IN IC New Const
Long Description	This IC Air-Loc Housing has a floating medium base porcelain socket with nickel-plated copper screw shell. It is shipped with a socket cap to protect against paint overspray. The Air-Loc housing stops infiltration and exfiltration of air, reducing heating and cooling costs.
Product Type	Housing

### Manufacturer Information

Brand	JUNO
GTIN	00661209272058
Manufacturers Part Number	V4ICW
UPC	661209272058

### Trade Size

aperture size	4 in
---------------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	6
Weight	4
Weight Per each	2.65

## Uses, Certifications, and Standards

Application	Education, Government, Hospitality, House of Worship, Residential, Retail
environmental conditions	Indoor
Mounting	Recessed
standard	cUL, UL