



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



V4ICW 4 Ic New Construction Housing

Lithonia Lighting

Catalog Number	V4ICW
Manufacturer	Lithonia Lighting
Description	This Ic Air-Loc Housing Has A Floating Medium Base Porcelain Socket With Nickel-Plated Copper Screw Shell. It Is Shipped With A Socket Cap To Protect Against Paint Overspray. The Air-Loc Housing Stops Infiltration and Exfiltration Of Air, Reducing Heating and Cooling Costs.
Weight per unit	2.7 (lbs/each)
Product Category	Halogen & Quartz Recessed Arch

Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	Round

Dimensions and Weight

Height	8
Length	14
Width	12

Descriptions

Construction	New Construction
Description	4IN LT FX HOUSING
extra long description	LITH V4IC W VuLite 4IN IC New Const
Long Description	This IC Air-Loc Housing has a floating medium base porcelain socket with nickel-plated copper screw shell. It is shipped with a socket cap to protect against paint overspray. The Air-Loc housing stops infiltration and exfiltration of air, reducing heating and cooling costs.
Product Type	Housing

Manufacturer Information

Brand	JUNO
GTIN	00661209272058
Manufacturers Part Number	V4ICW
UPC	661209272058

Trade Size

aperture size	4 in
---------------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight	4
Weight Per each	2.65

Uses, Certifications, and Standards

Application	Education, Government, Hospitality, House of Worship, Residential, Retail
environmental conditions	Indoor
Mounting	Recessed
standard	cUL, UL