



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



VAPOR1B065UNVD84 *Delisted* 8' Led 65W Vaportight 40K Dim

Sylvania-Ledvance

Catalog Number	VAPOR1B065UNVD84
Manufacturer	Sylvania-Ledvance
Description	Vapor Tight 1B, 65 Watts, 4000K, 120 277V, 0 10V Dimmable, 8 Foot, Etched Lens, Type V Distribution, Gray Painted Finish
Weight per unit	11.0 (lbs/each)
Product Category	Led Vapor Tight Lighting

Features

dimnable	Yes
housing	Polycarbonate (PC)
lumens	8,500
Material	Polycarbonate (PC)
total harmonic distortion	< 20
Voltage	120.00 - 277.00 V
Wattage	65.00

Material, Color, and Finish

color rendering index (cri)	>80
color temperature	4000

Descriptions

Description	*DELISTED* 8' LED 65W VAPORTIGHT 40K DIM
extra long description	SYL VAPOR1B/065UNVD840/96EC/GR/6035
Long Description	Vapor Tight 1B, 65 watts, 4000K, 120 277V, 0 10V dimmable, 8 foot, etched lens, type V distribution, gray painted finish
Product Type	VAPOR1B065UNVD84096ECGR 1/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135603556
Manufacturers Part Number	VAPOR1B/065UNVD840/96EC/GR/603
UPC	046135603556

Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
----------------------	-----------------------------------------------

Packaging

Carton	1
Weight Per each	10.99