



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



VHBLEDLD112WUNV 87W Led Highbay 50K 12000LM Dim 120-277V Wide *Cooper Lighting Solutions*

Catalog Number	VHBLEDLD112WUNV
Manufacturer	Cooper Lighting Solutions
Description	Led High Bay, White Enamel, CRS;Aluminum, 120/277 V Ac, 260 Ma, 100 W, 60000 H Average Life, 13009 LM Brightness (Lumens), 3500 K;4000 K;5000 K, 85, Non Dimmable, Wide Beam Spread, Surface/Chain Mount, 18-27/32 In Length, 14-19/32 In Width, 3-13/16 In Height, 15 LB
Weight per unit	15.0 (lbs/each)
Product Category	Led Highbay Lighting

Features

amperage rating	0.26 (at 277V)
Ballast Type	N/A
Lamp Type	LED

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	VHBLEDLD112WUNVL850CD1U
extra long description	CLS VHB-12-W-UNV-L850-CD-U VHB 120

Manufacturer Information

Brand	METALUX
GTIN	00080083785933
Manufacturers Part Number	VHB-12-W-UNV-L850-CD-U
UPC	080083785933

Taxonomies, Classifications, and Categories

Category Description	LED HIGHBAY, LOWBAY & INDUSTRIAL LIGHTING
Type	INDUSTRIAL

Packaging

Carton	1
Weight Per each	15

Uses, Certifications, and Standards

Mounting	High Bay
standard	UL/cUL Listed - Damp Location;RoHS Compliant