



LED 10W & 13 Wallpacks. Patent Pending thermal management system. 100,000 hour L70 lifespan. 5-year, no-compromise warranty.

Color: Bronze

Weight: 3.3 lbs

<b>Project:</b>	<b>Type:</b>
<b>Prepared By:</b>	<b>Date:</b>

Driver Info		LED Info	
Type:	Constant Current	Watts:	10W
120V:	0.1A	Color Temp:	5000K (Cool)
208V:	0.07A	Color Accuracy:	73 CRI
240V:	0.06A	L70 Lifespan:	100,000
277V:	0.05A	Lumens:	1,208
Input Watts:	12W	Efficacy:	97 LPW
Efficiency:	81%		

## Technical Specifications

### Listings

#### UL Listing:

Suitable for Wet Locations as a Downlight. Suitable for Damp Locations as an Uplight. Wall Mount only. Suitable for Mounting within 4ft. of ground.

#### IESNA LM-79 & IESNA LM-80 Testing:

RAB LED luminaires and LED components have been tested by an independent laboratory in accordance with IESNA LM-79 and LM-80.

### Electrical

#### THD:

10.8% at 120V, 13.8% at 277V

#### Power Factor:

98.5% at 120V, 92.1% at 277V

#### Driver:

Multi-chip 10W high output long life LED Driver Constant Current, Class II, 120V-240V, 50/60/ Hz, 350mA

### LED Characteristics

#### Lifespan:

100,000-hour LED lifespan based on IES LM-80 results and TM-21 calculations

#### Color Consistency:

7-step MacAdam Ellipse binning to achieve consistent fixture-to-fixture color

#### Color Stability:

LED color temperature is warrantied to shift no more than 200K in CCT over a 5 year period

#### Color Uniformity:

RAB's of CCT (Correlated color temperature) follows the guidelines of the American National Standard for Specifications for the Chromaticity of Solid State Lighting (SSL) Products, ANSI C78.377-2017.

#### Lumen Maintenance:

The LED will deliver 70% of its initial lumens at 100,000 hours of operation

### Construction

#### Finish:

Formulated for high-durability and long lasting color

#### Cold Weather Starting:

Minimum starting temperature is -40°C (-40°F)

#### Maximum Ambient Temperature:

Suitable for use in 40°C (104°F)

#### Housing:

Precision die cast aluminum housing, lens frame

#### Mounting:

Surface plate and Junction box

#### Green Technology:

Mercury and UV-free. RoHS compliant components.

#### Gaskets:

High Temperature Silicone

### Other

#### Patents:

The LPACK design is protected under patents in the U.S. Pat. D608,040, Canada Pat. 130,243, China Pat. 200930183252.2, and pending patents in Taiwan and Mexico.

#### Warranty:

RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at

#### Equivalency:

Equivalent to 70W Metal Halide

#### Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

### Optical

#### BUG Rating:

B1 U0 G0

## Dimensions



## Features

- High performance LED light engine
- Maintains 70% of initial lumens at 100,000 hours
- Weatherproof high temperature silicone gaskets
- Superior heat sinking with die cast aluminum housing and external fins
- 5-Year, No-Compromise Warranty

## Ordering Matrix

Family	Wattage	Color Temp	Sensor	Surface Plate	Surface Place	Finish	Photocell	Other Options
WPLED								
	<b>10</b> = 10W	<b>Blank</b> = 5000K (Cool)	<b>Blank</b> = No Sensor	<b>Blank</b> = No Surface Plate	<b>S</b> = Surface Plate	<b>Blank</b> = Bronze	<b>Blank</b> = No Photocell	<b>USA</b> = BAA Compliant
	<b>13</b> = 13W	<b>Y</b> = 3000K (Warm) <b>N</b> = 4000K (Neutral)	<b>MS</b> = Mini Sensor			<b>W</b> = White	<b>/PC</b> = 120V Button <b>/PCS</b> = 120V Swivel <b>/PC2</b> = 277V Button	<b>Blank</b> = Standard



LED 10W & 13 Wallpacks. Patent Pending thermal management system. 100,000 hour L70 lifespan. 5-year, no-compromise warranty.

Color: Bronze

Weight: 3.3 lbs

<b>Project:</b>	<b>Type:</b>
<b>Prepared By:</b>	<b>Date:</b>

Driver Info		LED Info	
Type:	Constant Current	Watts:	10W
120V:	0.1A	Color Temp:	5000K (Cool)
208V:	0.07A	Color Accuracy:	73 CRI
240V:	0.06A	L70 Lifespan:	100,000
277V:	0.05A	Lumens:	1,208
Input Watts:	12W	Efficacy:	97 LPW
Efficiency:	81%		

## Technical Specifications

### Listings

#### UL Listing:

Suitable for Wet Locations as a Downlight. Suitable for Damp Locations as an Uplight. Wall Mount only. Suitable for Mounting within 4ft. of ground.

#### IESNA LM-79 & IESNA LM-80 Testing:

RAB LED luminaires and LED components have been tested by an independent laboratory in accordance with IESNA LM-79 and LM-80.

### Electrical

#### THD:

10.8% at 120V, 13.8% at 277V

#### Power Factor:

98.5% at 120V, 92.1% at 277V

#### Driver:

Multi-chip 10W high output long life LED Driver Constant Current, Class II, 120V-240V, 50/60/ Hz, 350mA

### LED Characteristics

#### Lifespan:

100,000-hour LED lifespan based on IES LM-80 results and TM-21 calculations

#### Color Consistency:

7-step MacAdam Ellipse binning to achieve consistent fixture-to-fixture color

#### Color Stability:

LED color temperature is warrantied to shift no more than 200K in CCT over a 5 year period

#### Color Uniformity:

RAB's of CCT (Correlated color temperature) follows the guidelines of the American National Standard for Specifications for the Chromaticity of Solid State Lighting (SSL) Products, ANSI C78.377-2017.

#### Lumen Maintenance:

The LED will deliver 70% of its initial lumens at 100,000 hours of operation

### Construction

#### Finish:

Formulated for high-durability and long lasting color

#### Cold Weather Starting:

Minimum starting temperature is -40°C (-40°F)

#### Maximum Ambient Temperature:

Suitable for use in 40°C (104°F)

#### Housing:

Precision die cast aluminum housing, lens frame

#### Mounting:

Surface plate and Junction box

#### Green Technology:

Mercury and UV-free. RoHS compliant components.

#### Gaskets:

High Temperature Silicone

### Other

#### Patents:

The LPACK design is protected under patents in the U.S. Pat. D608,040, Canada Pat. 130,243, China Pat. 200930183252.2, and pending patents in Taiwan and Mexico.

#### Warranty:

RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at

#### Equivalency:

Equivalent to 70W Metal Halide

#### Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

### Optical

#### BUG Rating:

B1 U0 G0

## Dimensions



## Features

- High performance LED light engine
- Maintains 70% of initial lumens at 100,000 hours
- Weatherproof high temperature silicone gaskets
- Superior heat sinking with die cast aluminum housing and external fins
- 5-Year, No-Compromise Warranty

## Ordering Matrix

Family	Wattage	Color Temp	Sensor	Surface Plate	Surface Place	Finish	Photocell	Other Options
WPLED								
	<b>10</b> = 10W	<b>Blank</b> = 5000K (Cool)	<b>Blank</b> = No Sensor	<b>Blank</b> = No Surface Plate	<b>S</b> = Surface Plate	<b>Blank</b> = Bronze	<b>Blank</b> = No Photocell	<b>USA</b> = BAA Compliant
	<b>13</b> = 13W	<b>Y</b> = 3000K (Warm) <b>N</b> = 4000K (Neutral)	<b>MS</b> = Mini Sensor			<b>W</b> = White	<b>/PC</b> = 120V Button <b>/PCS</b> = 120V Swivel <b>/PC2</b> = 277V Button	<b>Blank</b> = Standard