



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WR83 #8 X 3" Phil BH Coarse Thread Drywall Screw

*L.H. Dottie CO.*

|                  |   |
|------------------|---|
| Catalog Number   | WR83  |
| Manufacturer     | L.H. Dottie CO.   |
| Description      | Drywall Screw, Steel, Bugle Head, 3 In Length, Yellow Zinc Plated, Unc-2A Thread Type, #8 Awg Diameter, Phillips Drive, 0.01 LB |
| Weight per unit  | 0.0120 (lbs/each)   |
| Product Category | Screws, Nuts, Bolts, Washers  |

### Features

|             |               |
|-------------|---------------|
| Head Type   | Bugle         |
| Point Type  | Self Piercing |
| Screw Type  | Drywall       |
| Thread Size | #8            |

### Dimensions and Weight

|      |           |
|------|-----------|
| Size | #8 x 3 IN |
|------|-----------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | #8 X 3" PHIL BH COARSE THREAD DRYWALL SCREW    |
| extra long description | DOTTIE WR83 8 X 3 Drywall Screws Ph            |
| Special Features       | Features: Wood Rocket, Invincibox Up to 2 Inch |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | LH DOTTIE      |
| GTIN  | 00781002162117 |
| UPC   | 781002162117   |

### Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps |
| Type                 | Bugle Head Wood Rocket Drywall Screw                   |

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 100   |
| Weight Per each | 0.012 |

### Uses, Certifications, and Standards

|             |                               |
|-------------|-------------------------------|
| Application | Drywall, Particle Board, Wood |
|-------------|-------------------------------|