



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1755 Enterprise Street
75751-0000, TX Athens
Phone: 903-675-7999
Fax: 903-675-9414



WSCL453PTC Wide Slide Inc/CFL/Led Dimmer 3W TC

Pass & Seymour/Legrand

Catalog Number	WSCL453PTC
Manufacturer	Pass & Seymour/Legrand
Description	Works With Select Dimmable CFL/Led or Incandescent Lighting Loads and Features A Sleek, Sculpted Ergonomic Design For Smooth, Easy Operation and Precise Control.
Weight per unit	0.3494 (lbs/each)
Product Category	Lighting Dimmers

Features

Connection Type	Screw Terminal
indoor/outdoor	Indoor
load	CFL, LED
Load Rating	120V 450W (CFL), 120V 450W (LED), 120V 700W (Halogen), 120V 700W (Incandescent)
Load Type	CFL, Halogen, Incandescent, LED
media	Yes
Mounting Type	Wall Box
Number of Gangs	1.0
Number of Switches	1.0
Poles	1
Switch Type	Slider, Rocker
Voltage	120 VAC
Voltage Rating	120
Wattage	450
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	Ivory, Light Almond, White
Finish	Matte

Descriptions

Description	WIDE SLIDE INC/CFL/LED DIMMER 3W TC
extra long description	P&S WSCL453PTC WIDE SLIDE INC/CFL/L
Features	Color Change Kit, Low-End Trim (Dim Range)
Long Description	Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.
Product Type	Wide Slide Inc/CFL/Led Dimmer 3W TC
Special Features	Preset



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1755 Enterprise Street
75751-0000, TX Athens
Phone: 903-675-7999
Fax: 903-675-9414

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007039535
Manufacturers Part Number	WSCL453PTC
UPC	785007039535

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Wide Slide

Packaging

Carton	1
Package	24
Weight Per each	0.3494

Uses, Certifications, and Standards

Application	Commercial/Residential
Enclosure	Thermoplastic
environmental conditions	Humidity: Less than 95% non condensing
Mounting	Box Mount
standard	cULus, RoHS