



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WT2B Wiretwist Wire Connector, WT2 Blue, 500/Bag

*Ideal*

Catalog Number	WT2B
Manufacturer	Ideal
Description	Wire Twist Connector, (3) #20 Awg Conductor Size, (3) #16 Awg Conductor Size, Blue Insulation Color, +221 °F Operating Temperature, 1 to 5 Conductors, 300 V, 0.75 LB
Weight per unit	0.7500 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

Material	Flame-retardant Polypropelene
Voltage Rating	300

### Material, Color, and Finish

Color	Blue
-------	------

### Descriptions

Description	WIRETWIST WIRE CONNECTOR, WT2 BLUE, 500/BAG
extra long description	IDEAL WT2-B WIRE-TWIST CONN.,BLUE,B
Features	With five, color-coded connectors designed to accommodate hundreds of different solid or stranded wire combinations, WireTwist Wire Connectors offer an economical connector that brings a lot of value in comfort and performance. The fixed, live-action, square-wire spring threads itself as it draws wires into the connector, creating a secure pressure grip. The rugged, thermoplastic shell withstands extreme environments. The deep, wide-throated skirt protects against flashover and turned back strands providing

### Manufacturer Information

Brand	Buchanan
GTIN	00781789610030
UPC	781789610030

### Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
----------------------	----------------------------------------

### Availability

minimum qty	500
-------------	-----

### Packaging

Carton	500
Package	10000
Weight Per each	0.75



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS