



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WT6B Wiretwist Wire Connector, WT6 Red, 250/Bag

*Ideal*

|                  |   |
|------------------|---|
| Catalog Number   | WT6B  |
| Manufacturer     | Ideal   |
| Description      | Buchanan, Wire Connector, Wiretwist, Conductor Range: 18 - 8 Awg, 2/14 Awg Min, 4/12 Awg Max, Number Of Conductors: 1 to 5, Material: Flame-Retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: WT6 |
| Weight per unit  | 1.6 (lbs/each)  |
| Product Category | Electrical Fixture Conn ( Nuts  |

### Features

|                      |                               |
|----------------------|-------------------------------|
| Material             | Flame-retardant Polypropelene |
| Number of Conductors | 1 to 5                        |
| Voltage Rating       | 600                           |

### Material, Color, and Finish

|       |     |
|-------|-----|
| Color | Red |
|-------|-----|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | WIRETWIST WIRE CONNECTOR, WT6 RED, 250/BAG   |
| extra long description | IDEAL WT6-B WIRE-TWIST CONN.,RED,BA  |
| Features               | With five, color-coded connectors designed to accommodate hundreds of different solid or stranded wire combinations, WireTwist Wire Connectors offer an economical connector that brings a lot of value in comfort and performance. The fixed, live-action, square-wire spring threads itself as it draws wires into the connector, creating a secure pressure grip. The rugged, thermoplastic shell withstands extreme environments. The deep, wide-throated skirt protects against flashover and turned back strands providing |
| Long Description       | Buchanan, Wire Connector, WireTwist, Conductor Range: 18 - 8 AWG, 2/14 AWG Min, 4/12 AWG MAX, Number Of Conductors: 1 to 5, Material: Flame-retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WT6  |
| Product Type           | Wire-Twist Conn., Red, Bag 250   |
| Special Features       | 1,000V Maximum In Fixtures And Signs;Deep, Wide-Throated Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection;Features: Five Color-Coded Models Cover Common Construction Wire Ranges;Fixed, Square-Wire Spring Threads Itself Creating A Secure Pressure Grip;Model Number: WT6;Ribbed Cap Provides Positive Grip For Fast, Easy Installation;Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 Degree C (221 Degree F);UL 486C Listed And CSA 22.2 #188 Certified                      |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Buchanan       |
| GTIN                      | 00781789610092 |
| Manufacturers Part Number | WT6-B          |
| sub brand                 | WireTwist      |
| UPC                       | 781789610092   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
|----------------------|--|

## Availability

|             |     |
|-------------|-----|
| minimum qty | 250 |
|-------------|-----|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 5000 |
| Weight Per each | 1.55 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | Insulating or Joining 1 or more conductors                       |
| environmental conditions | Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F) |
| standard                 | CSA C22.2 #188, UL 486C Listed, RoHS                             |