

# Specifications



## Eaton XBUT25BK

Eaton XB IEC terminal block, Screw connection single level-through-feed, Black, 12 AWG/2.5 mm<sup>2</sup> maximum wire

### General specifications

|                             |                             |
|-----------------------------|-----------------------------|
| <b>PRODUCT NAME</b>         | Eaton XB IEC terminal block |
| <b>CATALOG NUMBER</b>       | XBUT25BK                    |
| <b>UPC</b>                  | 786685231303                |
| <b>PRODUCT LENGTH/DEPTH</b> | 1.85 in                     |
| <b>PRODUCT HEIGHT</b>       | 2.17 in                     |
| <b>PRODUCT WIDTH</b>        | 0.2 in                      |
| <b>PRODUCT WEIGHT</b>       | 0.02 lb                     |
| <b>WARRANTY</b>             | 1 year                      |
| <b>CERTIFICATIONS</b>       | UL Listed<br>CSA Certified  |

## Product specifications

|                        |   |
|------------------------|---|
| <b>TYPE</b>            | IEC-XB Series                           |
| <b>AMPERAGE RATING</b> | 32A (IEC), 22A (EN), 28A (EN), 20A (UL) |
| <b>VOLTAGE RATING</b>  | IEC 800V, EN 700V, UL 600V              |

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XBUT25BK](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

