

Specifications



Eaton XBUT35

Eaton XB IEC terminal block, 16 mm Screw connection single level-through-feed, Gray, 8 AWG/6 mm² maximum wire, IEC 800V, EN 700V, UL 600V, IEC #24-8 AWG, EN #24-8 AWG, UL #24-8 AWG wire, IEC 57A, EN 40,50A, UL 50A

General specifications

| | |
|-----------------------------|-----------------------------|
| PRODUCT NAME | Eaton XB IEC terminal block |
| CATALOG NUMBER | XBUT35 |
| UPC | 782116905065 |
| PRODUCT LENGTH/DEPTH | 2.37 in |
| PRODUCT HEIGHT | 2.88 in |
| PRODUCT WIDTH | 0.63 in |
| PRODUCT WEIGHT | 0.02 lb |
| WARRANTY | 1 year |
| CERTIFICATIONS | CSA Certified UL Listed |



Powering Business Worldwide

Product specifications

| | |
|------------------------|---|
| TYPE | IEC-XB Series |
| AMPERAGE RATING | 527 (IEC), 40A (EN), 50A (EN), 50A (UL) |
| VOLTAGE RATING | IEC 800V, EN 700V, UL 600V |

Resources

| | |
|--------------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - XBUT35 |
|--------------------------------------|--|

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

