

Specifications



Eaton XBUT4FBEL24

Eaton XB IEC terminal block, Screw Connection Fuse Terminal Blocks, for 5 x 20 mm Fuse, Black, 10 AWG/4 mm² maximum wire, With LED 12–30V, 1–2.5 mA light

Product specifications

SPECIAL FEATURES	With LED 12–30V, 1–2.5 mA light
TYPE	IEC-XB Series
AMPERAGE RATING	6.30A (IEC), 6.30A (UL)
VOLTAGE RATING	UL 600V

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT4FBEL24
UPC	782116905225
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.24 in
PRODUCT WEIGHT	0.04 lb
WARRANTY	1 year
CERTIFICATIONS	CSA Certified UL Listed

EATON

Powering Business Worldwide

Specifications



Eaton XBUT4FBEL24

Eaton XB IEC terminal block, Screw Connection Fuse Terminal Blocks, for 5 x 20 mm Fuse, Black, 10 AWG/4 mm² maximum wire, With LED 12–30V, 1–2.5 mA light

Product specifications

SPECIAL FEATURES	With LED 12–30V, 1–2.5 mA light
TYPE	IEC-XB Series
AMPERAGE RATING	6.30A (IEC), 6.30A (UL)
VOLTAGE RATING	UL 600V

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT4FBEL24
UPC	782116905225
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.24 in
PRODUCT WEIGHT	0.04 lb
WARRANTY	1 year
CERTIFICATIONS	CSA Certified UL Listed

EATON

Powering Business Worldwide