

# Specifications



## Eaton XBUT4FBEL24

Eaton XB IEC terminal block, Screw Connection Fuse Terminal Blocks, for 5 x 20 mm Fuse, Black, 10 AWG/4 mm<sup>2</sup> maximum wire, With LED 12–30V, 1–2.5 mA light

### Product specifications

<b>SPECIAL FEATURES</b>	With LED 12–30V, 1–2.5 mA light
<b>TYPE</b>	IEC-XB Series
<b>AMPERAGE RATING</b>	6.30A (IEC), 6.30A (UL)
<b>VOLTAGE RATING</b>	UL 600V

### General specifications

<b>PRODUCT NAME</b>	Eaton XB IEC terminal block
<b>CATALOG NUMBER</b>	XBUT4FBEL24
<b>UPC</b>	782116905225
<b>PRODUCT LENGTH/DEPTH</b>	1.85 in
<b>PRODUCT HEIGHT</b>	2.17 in
<b>PRODUCT WIDTH</b>	0.24 in
<b>PRODUCT WEIGHT</b>	0.04 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	CSA Certified UL Listed

**EATON**

Powering Business Worldwide

# Specifications



## Eaton XBUT4FBEL24

Eaton XB IEC terminal block, Screw Connection Fuse Terminal Blocks, for 5 x 20 mm Fuse, Black, 10 AWG/4 mm<sup>2</sup> maximum wire, With LED 12–30V, 1–2.5 mA light

### Product specifications

<b>SPECIAL FEATURES</b>	With LED 12–30V, 1–2.5 mA light
<b>TYPE</b>	IEC-XB Series
<b>AMPERAGE RATING</b>	6.30A (IEC), 6.30A (UL)
<b>VOLTAGE RATING</b>	UL 600V

### General specifications

<b>PRODUCT NAME</b>	Eaton XB IEC terminal block
<b>CATALOG NUMBER</b>	XBUT4FBEL24
<b>UPC</b>	782116905225
<b>PRODUCT LENGTH/DEPTH</b>	1.85 in
<b>PRODUCT HEIGHT</b>	2.17 in
<b>PRODUCT WIDTH</b>	0.24 in
<b>PRODUCT WEIGHT</b>	0.04 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	CSA Certified UL Listed

**EATON**

Powering Business Worldwide