

Eaton XBUT6

Catalog Number: XBUT6

Eaton XB IEC terminal block, Screw connection single level through-feed terminal block, 8.2 mm, Gray, 8 AWG/6 mm² maximum wire, IEC 800V, EN 700V, UL 600V, IEC #24-8 AWG, EN #24-8 AWG, UL #24-8 AWG wire



General specifications

Product Name	Catalog Number
Eaton XB IEC terminal block	XBUT6
UPC	Product Length/Depth
782116904945	1.75 in
Product Height	Product Width
2.17 in	0.1 in
Product Weight	Warranty
0.01 lb	1 year
Certifications	
UL Listed	
CSA Certified	

defaultTaxonomyAttributeLabel

Type

IEC-XB Series

Amperage Rating

527 (IEC), 40A (EN), 50A (EN), 50A (UL)

Voltage rating

IEC 800V, EN 700V, UL 600V

Resources

Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Drawings

[XBUT6 3D Inventor](#)

[XBUT6 AutoCAD 2D Footprint \(mm\)](#)

[XBUT6 2D PDF](#)

[XBUT6 2D Drawing Xchange](#)

[XBUT6 AutoCAD 2D Footprint](#)

[XBUT6 3D Model Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - XBUT6](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)