



Powering Business Worldwide

pe.eaton.com

Screw Connection Double Level Blocks

XBUTT4

UPC:782116905324

Dimensions:

- **Height:** 2.75 IN
- **Length:** .24 IN
- **Width:** .03 IN

Weight:.04 LB

Warranties:

- 1 year

Specifications:

- **Type:** IEC-XB Series
- **Amperage Rating:** IEC 36A, UL 30A
- **Voltage Rating:** IEC 800V, UL 300V
- **Maximum Wire Size:** 10 AWG/4 mm²
- **Wire Size:** #26-10 AWG
- **Color:** Gray

Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBUTT4](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

Screw Connection Double Level Blocks

XBUTT4

UPC:782116905324

Dimensions:

- **Height:** 2.75 IN
- **Length:** .24 IN
- **Width:** .03 IN

Weight:.04 LB

Warranties:

- 1 year

Specifications:

- **Type:** IEC-XB Series
- **Amperage Rating:** IEC 36A, UL 30A
- **Voltage Rating:** IEC 800V, UL 300V
- **Maximum Wire Size:** 10 AWG/4 mm²
- **Wire Size:** #26-10 AWG
- **Color:** Gray

Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBUTT4](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data

