



PUSH BUTTONS

Dual Push Button Operator or Maintained Contact Unit

Class I, Groups B, C & D
Class II, Groups E, F & G
NEMA 3, 4, 7 & 9



XHDPB
XHDMC



XHDPBS
XHDMCS

FEATURES

- Die cast aluminum alloy. The barrels are all 3/4" NPSM thread. Maximum installation thickness 1 15/16" panel mount, 3/4" surface mount.
- Furnished standard with 120 volt slide base lamp. Also available for 6, 12, 24, 28, 48 and 60 volts. Specify when ordering.
- For use with BT contact blocks. Contact blocks can be stacked for multiple circuits. Contact blocks are not included with XHD operators. (See accessories at end of section)

FOR USE WITH SERIES BT CONTACT BLOCKS

Catalog #	Operator Description	Weight (lbs.)
XHDPB	Panel Mount - momentary*	1/2
XHDPBS	Surface Mount - momentary*	1/2
XHDMC	Maintained Contact, Panel Mount	1/2
XHDMCS	Maintained Contact, Surface Mount	1/2

*Two contacts in the BT contact block are actuated independently

LEGEND PLATES AT END OF SECTION