

Specifications

Eaton XJG104 SA

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 4" maximum conduit movement, 4" trade size



Photo is representative

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG expansion coupling
CATALOG NUMBER	XJG104 SA
UPC	782274916088
PRODUCT LENGTH/DEPTH	9.81 in
PRODUCT HEIGHT	6.62 in
PRODUCT WIDTH	6.62 in
PRODUCT WEIGHT	8.5 lb

Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

TYPE Expansion

	Locations
STANDARDS TYPE	NEC/CEC

CONDUIT TYPE	Rigid/IMC
TRADE SIZE	4"
CONDUIT MOVEMENT - MAX	4"
MATERIAL	Copper-free aluminum

Resources

BROCHURES	Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure
CATALOGS	Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page
CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification
INSTALLATION INSTRUCTIONS	IF 1508 - Assembly-Free XJG IF 343 - Type XJ Expansion Joints
SPECIFICATIONS AND DATASHEETS	Expansion and Deflection Couplings Eaton Specification Sheet - XJG104 SA

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

