

Specifications

Eaton XJG24

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Steel, 4" maximum conduit movement, 3/4" trade size



General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG expansion coupling
CATALOG NUMBER	XJG24
UPC	782274915746
PRODUCT LENGTH/DEPTH	8.3 in
PRODUCT HEIGHT	3.4 in
PRODUCT WIDTH	5.1 in
PRODUCT WEIGHT	2 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

TYPE	Expansion
CONDUIT TYPE	Rigid/IMC
TRADE SIZE	3/4"
CONDUIT MOVEMENT -	4"

MAX

MATERIALSteel

Resources

BROCHURES	Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure
CATALOGS	Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page
CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification
INSTALLATION INSTRUCTIONS	IF 1508 - Assembly-Free XJG IF 343 - Type XJ Expansion Joints
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XJG24 Expansion and Deflection Couplings

PROJECT NAME:**PROJECT NUMBER:****PREPARED BY:****DATE:**



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

