

# Eaton XJG24

Catalog Number: XJG24

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Steel, 4" maximum conduit movement, 3/4" trade size

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series XJG expansion coupling	XJG24
	UPC
	782274915746
Product Length/Depth	Product Height
8.3 in	3.4 in
Product Width	Product Weight
5.1 in	2 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Type

Expansion

### Conduit type

Rigid/IMC

### Trade size

3/4"

### Conduit movement - max

4"

### Material

Steel

## Resources

### Brochures

[Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure](#)

### Catalogs

[Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page](#)

### Certification reports

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification](#)

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification](#)

### Installation instructions

[IF 343 - Type XJ Expansion Joints](#)

[IF 1508 - Assembly-Free XJG](#)

### Specifications and datasheets

[Eaton Specification Sheet - XJG24](#)

[Expansion and Deflection Couplings](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)