

Eaton XJG24 SA

Catalog Number: XJG24 SA

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 4" maximum conduit movement, 3/4" trade size

General specifications



| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series XJG expansion coupling | XJG24 SA |
| | UPC |
| | 782274915760 |
| Product Length/Depth | Product Height |
| 8.3 in | 3.4 in |
| Product Width | Product Weight |
| 5.1 in | 1 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Type

Expansion

Conduit type

Rigid/IMC

Trade size

3/4"

Conduit movement - max

4"

Material

Copper-free aluminum

Resources

Brochures

[Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure](#)

Catalogs

[Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page](#)

Certification reports

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification](#)

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification](#)

Installation instructions

[IF 343 - Type XJ Expansion Joints](#)

[IF 1508 - Assembly-Free XJG](#)

Specifications and datasheets

[Expansion and Deflection Couplings](#)

[Eaton Specification Sheet - XJG24 SA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)