

# Specifications

## Eaton XJG54 SA



Photo is representative

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 4" maximum conduit movement, 1-1/2" trade size

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series XJG expansion coupling
<b>CATALOG NUMBER</b>	XJG54 SA
<b>UPC</b>	782274915883
<b>PRODUCT LENGTH/DEPTH</b>	8 in
<b>PRODUCT HEIGHT</b>	3.62 in
<b>PRODUCT WIDTH</b>	3.62 in
<b>PRODUCT WEIGHT</b>	2.55 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>TYPE</b>	Expansion
<b>CONDUIT TYPE</b>	Rigid/IMC
<b>TRADE SIZE</b>	1-1/2"
<b>CONDUIT MOVEMENT - MAX</b>	4"
<b>MATERIAL</b>	Copper-free aluminum

## Resources

<b>BROCHURES</b>	<a href="#">Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure</a>
<b>CATALOGS</b>	<a href="#">Crouse-Hinds series XIG Conduit Expansion Couplings for Rigid/IMC catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">XIG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification</a> <a href="#">XIG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification</a>
<b>INSTALLATION INSTRUCTIONS</b>	<a href="#">IF 343 - Type XJ Expansion Joints</a> <a href="#">IF 1508 - Assembly-Free XIG</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Expansion and Deflection Couplings</a> <a href="#">Eaton Specification Sheet - XIG54 SA</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

# Specifications

## Eaton XJG54 SA



Photo is representative

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 4" maximum conduit movement, 1-1/2" trade size

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series XJG expansion coupling
<b>CATALOG NUMBER</b>	XJG54 SA
<b>UPC</b>	782274915883
<b>PRODUCT LENGTH/DEPTH</b>	8 in
<b>PRODUCT HEIGHT</b>	3.62 in
<b>PRODUCT WIDTH</b>	3.62 in
<b>PRODUCT WEIGHT</b>	2.55 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>TYPE</b>	Expansion
<b>CONDUIT TYPE</b>	Rigid/IMC
<b>TRADE SIZE</b>	1-1/2"
<b>CONDUIT MOVEMENT - MAX</b>	4"
<b>MATERIAL</b>	Copper-free aluminum

## Resources

<b>BROCHURES</b>	<a href="#">Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure</a>
<b>CATALOGS</b>	<a href="#">Crouse-Hinds series XIG Conduit Expansion Couplings for Rigid/IMC catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">XIG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification</a> <a href="#">XIG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification</a>
<b>INSTALLATION INSTRUCTIONS</b>	<a href="#">IF 343 - Type XJ Expansion Joints</a> <a href="#">IF 1508 - Assembly-Free XIG</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Expansion and Deflection Couplings</a> <a href="#">Eaton Specification Sheet - XIG54 SA</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.