

Eaton XTAE032C10T032

Catalog Number: XTAE032C10T032

Eaton XT IEC electronic motor starter, Full voltage non-reversing IEC starter, 32 A, 24 V 50/60 Hz, 1NO, C frame, 45 mm, 24-32 A, Screw terminals



Photo is representative

General specifications

Product Name	Catalog Number
Eaton XT IEC electronic motor starter	XTAE032C10T032
UPC	Product Length/Depth
782116864126	5.5 in
Product Height	Product Width
5.37 in	4.15 in
Product Weight	Warranty
2.35 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
RoHS Compliant	IEC 60947
ATEX Compliant	CSA Certified
	EN 60947
Catalog Notes	
Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)	

Amperage Rating

32A

Overload range

24-32 A

Type

Full voltage non-reversing IEC starter

Frame size

45 mm

Terminals

Screw terminals

Coil

24 Vac, 50/60 Hz

Contact configuration

1 NO

Frame

C

Catalogs[Eaton's Volume 5—Motor Control and Protection](#)**Specifications and datasheets**[Eaton Specification Sheet - XTAE032C10T032](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)