

# Eaton XTCE032C10H

Catalog Number: XTCE032C10H

Eaton XT IEC contactor, 32A, 240 Vac, 50 Hz, 277V 60 Hz, 1NO, 32A, Frame C, 45 mm, 50-60 Hz, 3, 5, 5/ 10, 10, 20, 25 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

## General specifications



### Product Name

Eaton XT IEC contactor

### Catalog Number

XTCE032C10H

### UPC

782116486144

### Product Length/Depth

3.425 in

### Product Height

3.898 in

### Product Width

1.85 in

### Product Weight

0.9 lb

### Warranty

1 year

### Compliances

RoHS Compliant

CE Marked

### Certifications

IEC 60947

CSA Certified

EN 60947

UL Listed

### Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## Product specifications

### Amperage Rating

32A

### HP rating - max

3, 5, 5/ 10, 10, 20, 25 hp (1/3PH  
@ 115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

50-60 Hz

### Frame size

45 mm

### Terminals

Screw terminals

### Coil voltage

240-277 Vac, 50/60 Hz

### Contact configuration

1 NO

### Continuous ampere rating

32 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCE\\_C 3D Model Xchange](#)

[XTCE\\_C AutoCAD 2D Footprint](#)

[XTCE\\_C 2D Drawing Xchange](#)

[XTCE\\_C 2D PDF](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTCE032C10H](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XTCE032C10H

Catalog Number: XTCE032C10H

Eaton XT IEC contactor, 32A, 240 Vac, 50 Hz, 277V 60 Hz, 1NO, 32A, Frame C, 45 mm, 50-60 Hz, 3, 5, 5/ 10, 10, 20, 25 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

## General specifications



### Product Name

Eaton XT IEC contactor

### Catalog Number

XTCE032C10H

### UPC

782116486144

### Product Length/Depth

3.425 in

### Product Height

3.898 in

### Product Width

1.85 in

### Product Weight

0.9 lb

### Warranty

1 year

### Compliances

RoHS Compliant

CE Marked

### Certifications

IEC 60947

CSA Certified

EN 60947

UL Listed

### Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## Product specifications

### Amperage Rating

32A

### HP rating - max

3, 5, 5/ 10, 10, 20, 25 hp (1/3PH  
@ 115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

50-60 Hz

### Frame size

45 mm

### Terminals

Screw terminals

### Coil voltage

240-277 Vac, 50/60 Hz

### Contact configuration

1 NO

### Continuous ampere rating

32 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCE\\_C 3D Model Xchange](#)

[XTCE\\_C AutoCAD 2D Footprint](#)

[XTCE\\_C 2D Drawing Xchange](#)

[XTCE\\_C 2D PDF](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTCE032C10H](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)